

Detailed Specifications

Frame Size:	95[mm]
Frame Width:	33[mm]
Nominal Voltage:	24[V]
Max. Air Flow:	24.7[CFM]
Max. Static Pressure:	0.9[In H2O]
Speed:	3200[min-1]
Noise:	51.5[dB]
Life Expectancy:	25 degree C 100,000 Hours[L10]
Bearing Type:	Ball Bearing
Operating Voltage Lower:	10[V]
Operating Voltage Upper:	27.6[V]
Nominal Current:	0.33[A]
Input Power:	7.92[W]
Mass:	210[g]

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[BG0903-B053-000-00](#)