

Detailed Specifications

Frame Size:	100[mm]
Frame Width:	32[mm]
Nominal Voltage:	12[V]
Max. Air Flow:	28.2[CFM]
Max. Static Pressure:	0.7[In H2O]
Speed:	2250[min-1]
Noise:	48.5[dB]
Life Expectancy:	25 degree C 100,000 Hours[L10]
Bearing Type:	Ball Bearing
Operating Voltage Lower:	6[V]
Operating Voltage Upper:	13.8[V]
Nominal Current:	0.65[A]
Input Power:	7.8[W]
Mass:	270[g]

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[BG1203-B044-00S-00](#)