

Detailed Specifications

Frame Size:	45[mm]
Frame Width:	15[mm]
Nominal Voltage:	12[V]
Max. Air Flow:	3.5[CFM]
Max. Static Pressure:	0.8[In H2O]
Speed:	7500[min^{-1}]
Noise:	43[dB]
Life Expectancy:	25 degree C 50,000 Hours[L10]
Bearing Type:	Ball Bearing
Operating Voltage Lower:	10.2[V]
Operating Voltage Upper:	13.8[V]
Nominal Current:	0.19[A]
Input Power:	2.28[W]
Mass:	25[g]

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[BM4515-04W-B59-L00](#)