

Detailed Specifications

Frame Size:	175[mm]
Frame Depth:	69[mm]
Nominal Voltage:	48[V]
Max. Air Flow:	453[CFM]
Max. Static Pressure:	3.6[In H2O]
Speed:	4600[rpm]
Noise:	73[dB]
Life Expectancy:	40 degree C 70,000 Hours[L10]
Bearing Type:	Ball Bearing
Operating Voltage - Lower:	36[V]
Operating Voltage - Upper:	72[V]
Nominal Current:	1.4[A]
Input Power:	67.2[W]
Mass:	1000[g]

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[F175A2-062-D0740](#)