

Detailed Specifications

Frame Width:	172[mm]
Frame Height:	172[mm]
Frame Depth:	51[mm]
Max. Air Flow:	604[CFM]
Max. Air Flow:	16.91[m3 per min]
Max. Static Pressure:	6.05[In H2O]
Max. Static Pressure:	1507[Pa]
Fan Speed:	9300[RPM]
Noise:	82[dB]
Life Expectancy:	40 degree C 70,000 Hours[L10]
Bearing Type:	Ball Bearing
Speed Control:	PWM
Nominal Voltage:	48[V]
Operating Voltage 0 Lower:	30[V]
Operating Voltage 0 Upper:	72[V]
Current:	4.2[A]
Input Power:	201.6[W]
Mass:	1050[g]
Tach / Locked Rotor Output:	Tach Output

PWM Speed Control Fans

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[R172A0-051-D0790](#)