

QL 3 SAKA10**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Similar to illustration

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

General ordering data

Version	SAK Series, Cross-connector, for cross-connection link, Number of poles: 3
Order No.	0135600000
Type	QL 3 SAKA10
GTIN (EAN)	4008 190032081
Qty.	50 pc(s).

QL 3 SAKA10

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Height	6 mm	Height (inches)	0.236 inch
Width	31.8 mm	Width (inches)	1.252 inch
Net weight	2.5 g		

Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Material data

Material	Cu Zn	Colour	grey
----------	-------	--------	------

System specifications

Version	for cross-connection link
---------	---------------------------

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	when screwed in		

Cross-connector

Number of cross-connected terminals	3	Rated current, 2-pole	47 A
Rated current, multi-pole	36 A	Type	Cross-connector

Dimensions

Pitch in mm (P)	12 mm
-----------------	-------

General

Installation advice	Direct mounting	Number of poles	3
---------------------	-----------------	-----------------	---

Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ECLASS 9.0	27-14-11-40
ECLASS 9.1	27-14-11-40	ECLASS 10.0	27-14-11-40
ECLASS 11.0	27-14-11-40		

Approvals

ROHS	Conform
------	---------

Downloads

User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[0135600000](#)