

**TW SAKB/C/T1****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

End plates are fitted to the open side of the last modular terminal before the end bracket. The use of an end plate ensures the function of the modular terminal and the specified rated voltage. It guarantees protection against contact with live parts and makes the final terminal finger-proof.

**General ordering data**

|            |                                                             |
|------------|-------------------------------------------------------------|
| Version    | SAK Series, Partition plate, 1.5 mm, beige, Direct mounting |
| Order No.  | <a href="#">0242960000</a>                                  |
| Type       | TW SAKB/C/T1                                                |
| GTIN (EAN) | 4008190104092                                               |
| Qty.       | 20 pc(s).                                                   |

## TW SAKB/C/T1

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 42.5 mm | Depth (inches)  | 1.673 inch |
| Height     | 75 mm   | Height (inches) | 2.953 inch |
| Width      | 1.5 mm  | Width (inches)  | 0.059 inch |
| Net weight | 5.385 g |                 |            |

## Temperatures

|                                  |                |                                  |        |
|----------------------------------|----------------|----------------------------------|--------|
| Storage temperature              | -25 °C...55 °C | Continuous operating temp., min. | -50 °C |
| Continuous operating temp., max. | 100 °C         |                                  |        |

## Material data

|                           |       |        |       |
|---------------------------|-------|--------|-------|
| Material                  | PA 66 | Colour | beige |
| UL 94 flammability rating | V-2   |        |       |

## System specifications

|         |                    |
|---------|--------------------|
| Version | Intermediate plate |
|---------|--------------------|

## Additional technical data

|                     |                 |         |    |
|---------------------|-----------------|---------|----|
| Installation advice | Direct mounting | Snap-on | No |
|---------------------|-----------------|---------|----|

## General

|                     |                 |
|---------------------|-----------------|
| Installation advice | Direct mounting |
|---------------------|-----------------|

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000886    | ETIM 7.0    | EC000886    |
| ETIM 8.0    | EC000886    | ECLASS 9.0  | 27-14-11-92 |
| ECLASS 9.1  | 27-14-11-33 | ECLASS 10.0 | 27-14-11-92 |
| ECLASS 11.0 | 27-14-11-92 | ECLASS 12.0 | 27-14-11-92 |

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Downloads

|                    |                                                 |
|--------------------|-------------------------------------------------|
| User Documentation | <a href="#">StorageConditionsTerminalBlocks</a> |
| Catalogues         | <a href="#">Catalogues in PDF-format</a>        |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[0242960000](#)