

VP 7-MS65**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	VPMS (blanking plug in brass), Blanking plug, PG 7, 5 mm, Brass, nickel-plated
Order No.	0521600000
Type	VP 7-MS65
GTIN (EAN)	4008190011871
Qty.	100 pc(s).

VP 7-MS65

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Height	7.5 mm	Height (inches)	0.295 inch
Length	7.5 mm	Length (inches)	0.295 inch
Diameter	15 mm	Net weight	3.28 g

Temperatures

Operating temperature	-40 °C...100 °C
-----------------------	-----------------

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

General information

Cable glands	PG	External thread	PG 7
Halogen	No	Head diameter	15 mm
Length of thread	5 mm	Material	Brass, nickel-plated
O-Ring	NBR	Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C	Protection degree	IP68 - 5 bar (30 min.)
Sealing	NBR		

Classifications

ETIM 6.0	EC000451	ETIM 7.0	EC000451
ETIM 8.0	EC000451	ECLASS 9.0	27-14-44-25
ECLASS 9.1	27-14-44-33	ECLASS 10.0	27-14-44-25
ECLASS 11.0	27-14-44-25		

Approvals

Approvals



ROHS	Conform
------	---------

Downloads


Engineering Data	CAD data – STEP
Engineering Data	EPLAN, WSCAD
Catalogues	Catalogues in PDF-format
Brochures	

VP 7-MS65

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[0521600000](#)