

**CLI RH 20-10 CLI R 10****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

The CableLine range of wire and cable marker products provides users with solutions for the most diverse applications. The range of applications extends from narrow wires right up to cables with large outside diameters.

**General ordering data**

|            |                                    |
|------------|------------------------------------|
| Version    | CableLine, Mounting mandrel holder |
| Order No.  | <a href="#">0563600000</a>         |
| Type       | CLI RH 20-10 CLI R 10              |
| GTIN (EAN) | 4008 1900 18436                    |
| Qty.       | 1 pc(s).                           |

## CLI RH 20-10 CLI R 10

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |       |                 |            |
|------------|-------|-----------------|------------|
| Depth      | 28 mm | Depth (inches)  | 1.102 inch |
| Height     | 55 mm | Height (inches) | 2.165 inch |
| Width      | 55 mm | Width (inches)  | 2.165 inch |
| Net weight | 44 g  |                 |            |

## Temperatures

|                             |              |
|-----------------------------|--------------|
| Operating temperature range | -40...100 °C |
|-----------------------------|--------------|

## General data

|                                   |              |                                              |                    |
|-----------------------------------|--------------|----------------------------------------------|--------------------|
| Colour                            | blue         | Halogen                                      | Yes                |
| Material                          | Polyamide    | Material colour according to resistance code | 6                  |
| Operating temperature range       | -40...100 °C | Operating temperature range, max.            | 100 °C             |
| Operating temperature range, min. | -40 °C       | Recommended industries                       | Process, Machinery |
| UL 94 flammability rating         | V-0          | Width                                        | 55 mm              |

## Conductor and cable markers

|         |     |
|---------|-----|
| Halogen | Yes |
|---------|-----|

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001288    | ETIM 7.0    | EC001288    |
| ETIM 8.0    | EC001288    | ECLASS 9.0  | 27-40-06-29 |
| ECLASS 9.1  | 27-40-06-29 | ECLASS 10.0 | 27-40-06-29 |
| ECLASS 11.0 | 27-28-11-04 |             |             |

## Downloads

|                  |                                          |
|------------------|------------------------------------------|
| Engineering Data | <a href="#">WSCAD</a>                    |
| Catalogues       | <a href="#">Catalogues in PDF-format</a> |

### CLI RH 20-10 CLI R 10

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

### Example of use



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[0563600000](#)