

CRIMPFIX L PZ3**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

- For automatic stripping and crimping
- Time-saving and efficient processing
- Easily adjustable to the respective cross-section range
- Stripping and crimping in one work step
- The processing of sleeves or contacts from other manufacturers can cause machine failures and defects!

General ordering data

Version	Automatic stripper and crimper
Order No.	1243790000
Type	CRIMPFIX L PZ3
GTIN (EAN)	4050118031966
Qty.	1 pc(s).

CRIMPFIX L PZ3**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	330 mm	Depth (inches)	12.992 inch
Height	460 mm	Height (inches)	18.11 inch
Width	390 mm	Width (inches)	15.354 inch
Net weight	34,000 g		

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

PW65 maintenance - automatic stripping/crimping

Compressed-air connection	5 - 5.5 bar	Consumables	loose cable lugs
Crimping length	8 mm	Drive	Electropneumatic
Electrical connection	100-240 V / 50/60 Hz / 110 VA	Length of wire-end ferrule	14 mm
Pulse time	approx. 1 s	Stripping range	0.5 - 2.5 mm ² (~AWG 20-14)
Wire end ferrules cross-section, max.	2.5 mm ²	Wire end ferrules cross-section, min.	0.5 mm ²

Classifications

ETIM 6.0	EC002778	ETIM 7.0	EC002778
ETIM 8.0	EC002778	ECLASS 9.0	17-13-01-01
ECLASS 9.1	17-13-01-01	ECLASS 10.0	17-13-01-01
ECLASS 11.0	17-13-01-01	ECLASS 12.0	17-13-01-01

Approvals

Approvals



ROHS Conform

Downloads

User Documentation	Manual
Catalogues	Catalogues in PDF-format

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1243790000](#)