

**HDC XX6A01 MFSM12X-2000****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Compact**

The new two-pole bus module is extremely compact and can accommodate both megabit and gigabit data inserts. It enables the connection of 2 Gigabit Cat 6A cables (10 gigabit) to one module.

**General ordering data**

| Version    |                            |
|------------|----------------------------|
| Version    | Data use                   |
| Order No.  | <a href="#">2450442000</a> |
| Type       | HDC XX6A01 MFSM12X-2000    |
| GTIN (EAN) | 4050118464634              |
| Qty.       | 1 pc(s).                   |

## HDC XX6A01 MFSM12X-2000

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |        |
|------------|--------|
| Net weight | 0.01 g |
|------------|--------|

## Temperatures

|                   |                  |
|-------------------|------------------|
| Limit temperature | -40 °C ... 90 °C |
|-------------------|------------------|

## Environmental Product Compliance

|            |                |      |                                   |
|------------|----------------|------|-----------------------------------|
| REACH SVHC | Lead 7439-92-1 | SCIP | 2ac5c63f-7f5e-465a-860d-49cfb7bbe |
|------------|----------------|------|-----------------------------------|

## General data

|                     |                    |                       |                        |
|---------------------|--------------------|-----------------------|------------------------|
| Cable length        | 20 m               | Category              | Cat. 6A                |
| Coding              | X                  | Contact surface       | Au (Gold)              |
| Insulation strength | $\geq 10^8 \Omega$ | Module side version   | Male                   |
| Number of poles     | 8                  | Opposite side version | Female, straight, M12X |
| Pollution severity  | 2                  | Rated current         | 0.5 A                  |
| Rated voltage       | 50 V               | Transmission rate     | 10 Gbps, 10 Gbit/s     |
| Type                | Pin                |                       |                        |

## Cable technical specifications

|                  |                                                                                        |        |
|------------------|----------------------------------------------------------------------------------------|--------|
| Cable length     | 20 m                                                                                   |        |
| Colour coding    | white / orange, orange, white / green, green, white / brown, brown, white / blue, blue |        |
| Halogen          | No                                                                                     |        |
| Insulation       | Expanded                                                                               |        |
| Outside diameter | 8.1 mm $\pm$ 0.5                                                                       |        |
| Outside diameter | Diameter                                                                               | 8.1 mm |
|                  | Signs                                                                                  | $\pm$  |
|                  | Tolerance                                                                              | 0.5    |
| Sheath material  | Radox EM 104                                                                           |        |
| Sheathing colour | blue                                                                                   |        |
| Shielded         | Yes                                                                                    |        |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002599    | ETIM 7.0    | EC002599    |
| ETIM 8.0    | EC002599    | ECLASS 9.0  | 27-06-03-07 |
| ECLASS 9.1  | 27-06-03-08 | ECLASS 10.0 | 27-06-03-07 |
| ECLASS 11.0 | 27-06-03-07 | ECLASS 12.0 | 27-06-03-07 |

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Downloads

|                  |                                          |
|------------------|------------------------------------------|
| Engineering Data | <a href="#">CAD data – STEP</a>          |
| Catalogues       | <a href="#">Catalogues in PDF-format</a> |

## HDC XX6A01 MFSM12X-2000

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

# Drawings

|     |   |               |   |     |
|-----|---|---------------|---|-----|
| M12 | 1 | White, Orange | 1 | M12 |
|     | 2 | Orange        | 2 |     |
|     | 3 | White, Green  | 3 |     |
|     | 4 | Green         | 4 |     |
|     | 5 | White, Brown  | 5 |     |
|     | 6 | Brown         | 6 |     |
|     | 7 | White, Blue   | 7 |     |
|     | 8 | Blue          | 8 |     |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[2450442000](#)