

HDC C MHX BM10.0AG**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Crimps provide a electrical and mechanical connection between wire and contact that is both secure and reliable. The optimal crimp connection is gas-tight and corrosion-resistant.

General ordering data

Version	Heavy-duty connectors, Crimp contact, Female, Conductor cross-section, max.: 10, turned, Copper alloy
Order No.	2494560000
Type	HDC C MHX BM10.0AG
GTIN (EAN)	4050118504538
Qty.	25 pc(s).

HDC C MHX BM10.0AG**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight	2.78 g
------------	--------

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1	SCIP	6eabd5ae-2d6b-409e-8bdf-87c27ee1
------------	----------------	------	----------------------------------

General data

Conductor cross-section, max.	10 mm ²	Contact diameter, male Ø	4 mm
Contact material	Copper alloy	Cross-section for connected wire	10 mm ²
Material	Copper alloy	Plugging cycles	≥ 500
Production methods	turned	Surface finish	silver
Type	Female	Type of connection	Crimp connection
Volume resistance	≤1 mΩ		

Classifications

ETIM 6.0	EC000796	ETIM 7.0	EC000796
ETIM 8.0	EC000796	ECLASS 9.0	27-44-02-04
ECLASS 9.1	27-44-02-04	ECLASS 10.0	27-44-02-04
ECLASS 11.0	27-44-02-04	ECLASS 12.0	27-44-02-04

Important note

Product information	Stripping length 11 - 12 mm
---------------------	-----------------------------

Approvals

ROHS	Conform
------	---------

Downloads


Engineering Data	EPLAN
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN FL FIELDWIRING EN

HDC C MHX BM10.0AG

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[2494560000](#)