

**EL 60 MM SW 30M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Customised identification: EL**

The endless variations of MultiMark markers make them an economical alternative to conventional tag rails or special labels. For any given width, the height can be precisely configured by the software to match the respective markers perfectly. A blade is used to cut the labels individually to the specified size. Perfect for producing large labels for function blocks or complete terminal blocks.

**Your benefits with MultiMark**

- “Different materials for various requirements”
- Can be used with equipment from many manufacturers
- Device markers with a familiar design

**General ordering data**

|                    |                                                       |
|--------------------|-------------------------------------------------------|
| Version            | THM, Device markers, 60 x , black                     |
| Order No.          | <a href="#">2528420000</a>                            |
| Type               | EL 60 MM SW 30M                                       |
| GTIN (EAN)         | 4050118539318                                         |
| Qty.               | 1 pc(s).                                              |
| compatible printer | <a href="#">2599430000</a> <a href="#">2599440000</a> |

**EL 60 MM SW 30M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

|            |           |                 |              |
|------------|-----------|-----------------|--------------|
| Depth      | 0.1 mm    | Depth (inches)  | 0.004 inch   |
| Height     | 60 mm     | Height (inches) | 2.362 inch   |
| Length     | 30,000 mm | Length (inches) | 1,181.1 inch |
| Net weight | 499 g     |                 |              |

**Temperatures**

|                             |              |
|-----------------------------|--------------|
| Operating temperature range | -40...120 °C |
|-----------------------------|--------------|

**General data**

|                                   |                   |                                   |                             |
|-----------------------------------|-------------------|-----------------------------------|-----------------------------|
| Adhesive                          | Acrylate adhesive | Approval acc. to UL 969           | Yes                         |
| Colour                            | black             | Halogen                           | No                          |
| Length                            | 30,000 mm         | Material                          | Polyester                   |
| Number per roll                   | 1                 | Operating temperature range       | -40...120 °C                |
| Operating temperature range, max. | 120 °C            | Operating temperature range, min. | -40 °C                      |
| UL 94 flammability rating         | V-0               | Version                           | halogen-free, Self-adhesive |

**Device markers**

|         |    |
|---------|----|
| Halogen | No |
|---------|----|

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001288    | ETIM 7.0    | EC001288    |
| ETIM 8.0    | EC001288    | ECLASS 9.0  | 27-40-06-29 |
| ECLASS 9.1  | 27-40-06-29 | ECLASS 10.0 | 27-40-06-29 |
| ECLASS 11.0 | 27-28-11-04 | ECLASS 12.0 | 27-28-11-04 |

**Important note**

|                     |                                           |
|---------------------|-------------------------------------------|
| Product information | External roll holder 1302920000 necessary |
|---------------------|-------------------------------------------|

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|                  |                                          |
|------------------|------------------------------------------|
| Engineering Data | <a href="#">EPLAN</a>                    |
| Catalogues       | <a href="#">Catalogues in PDF-format</a> |

### EL 60 MM SW 30M

**Weidmüller Interface GmbH & Co. KG**


Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[2528420000](#)