

FP ENC AS 178 3C**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The FieldPower® housings are highly robust and meet the highest UL flammability class 5 VA.

- The "TS 35 PT6" mounting rail module and PT6 contact unit are easy to snap on.
- Hinged seals allow pre-assembled plug cables to also be used.
- The high cover versions enable the device to be installed.

For cable seals consult accessories.

General ordering data

Order No.	2632840000
Type	FP ENC AS 178 3C
GTIN (EAN)	4050118664515
Qty.	1 pc(s).

FP ENC AS 178 3C

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	178 mm	Depth (inches)	7.008 inch
Height	191 mm	Height (inches)	7.52 inch
Width	280 mm	Width (inches)	11.024 inch
Net weight	3,524.53 g		

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...85 °C
---------------------	----------------	-----------------------	----------------

General specifications

Protection degree	IP65, in closed state	Silicone	No
Material	Aluminium	Colour	Silver grey, Aluminium
Lid attachment	TX20 screws	Enclosure attachment	Fixing lugs

Classifications

ETIM 6.0	EC000261	ETIM 7.0	EC000261
ETIM 8.0	EC000261	ECLASS 9.0	27-18-01-01
ECLASS 9.1	27-18-92-90	ECLASS 10.0	27-18-01-01
ECLASS 11.0	27-18-01-01	ECLASS 12.0	27-18-01-01

Approvals

ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	Manufacturer's Declaration FieldPower® Enclosure parts
Engineering Data	CAD data – STEP
User Documentation	Manual FieldPower® enclosure size 3
Catalogues	Catalogues in PDF-format

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[2632840000](#)