

HDC MMARK 4**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

In addition to heavy-duty connectors, RockStar® includes the appropriate accessories for effective, functional and safe system cabling; e.g. coding systems, shield clamps, cover plates and replacement seals

General ordering data

Version	Marking tags, Heavy duty connector assemblies
Order No.	2710590000
Type	HDC MMARK 4
GTIN (EAN)	4050118783902
Qty.	640 pc(s).
compatible printer	2438520000 2438510000

HDC MMARK 4

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Width	3.1 mm	Width (inches)	0.122 inch
Net weight	0.174 g		

Temperatures

Limit temperature	-40 °C ... 125 °C
-------------------	-------------------

General data

Material	PA 66, POM	Version	For ModuPlug MHE 4X module
----------	------------	---------	----------------------------

General data

Colour	white	Material	PA 66, POM
Operating temperature range, max.	125 °C	Operating temperature range, min.	-40 °C
Printed characters	neutral	UL 94 flammability rating	V-2, HB
Version	For ModuPlug MHE 4X module	Width	3.1 mm

Classifications

ETIM 6.0	EC000761	ETIM 7.0	EC000761
ETIM 8.0	EC000761	ECLASS 9.0	27-14-11-37
ECLASS 9.1	27-14-11-37	ECLASS 10.0	27-14-11-37
ECLASS 11.0	27-28-11-01	ECLASS 12.0	27-28-11-01

Downloads

Software	Project Examples and Templates – Configuration file M-Print PRO
Catalogues	Catalogues in PDF-format

HDC MMARK 4

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[2710590000](#)