

SDIS 1.0X4.5X175**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



VDE insulated slot-head screwdriver, SDI DIN 7437, ISO 2380/2, drive output acc. to DIN 5264, ISO 2380/1.
SoftFinish grip

General ordering data

Version	Screwdriver, Blade width (B): 4.5 mm, Blade length: 175 mm, Blade thickness (A): 1 mm
Order No.	2749840000
Type	SDIS 1.0X4.5X175
GTIN (EAN)	4050118897043
Qty.	1 pc(s).

SDIS 1.0X4.5X175**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.comwww.weidmueller.com**Technical data****Dimensions and weights**

Width	286 mm	Width (inches)	11.26 inch
Net weight	64 g		

Technical data

Description of article	VDE-insulated screwdriver with slotted blade 1.0 x 4.5 x 175
------------------------	--

Screwing tools

Blade length	175 mm	Blade thickness (A)	1 mm
Blade type	B	Blade width (B)	4.5 mm
Form	Slotted		

Classifications

ETIM 6.0	EC000158	ETIM 7.0	EC000158
ETIM 8.0	EC000158	ECLASS 9.0	21-04-04-07
ECLASS 9.1	21-04-04-07	ECLASS 10.0	21-04-04-07
ECLASS 11.0	21-04-04-07	ECLASS 12.0	21-04-04-07

Downloads

Catalogues	Catalogues in PDF-format
------------	--

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[2749840000](#)