

SDIPM PH2 X 100**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



VDE insulated screwdriver sets, for working on live parts up to 1000 V AC and 1500 V DC, DIN EN 60900. IEC 900. Each piece is "GS" safety tested. Blade made from fully hardened, high-alloy chromium-vanadium-molybdenum steel, gun-metal finish.

General ordering data

Version	Mounting tool, Blade length: 100 mm
Order No.	2749970000
Type	SDIPM PH2 X 100
GTIN (EAN)	4050118897272
Qty.	1 pc(s).

SDIPM PH2 X 100**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technical data**Dimensions and weights**

Width	215 mm	Width (inches)	8.465 inch
Net weight	93 g		

Screwing tools

Blade length	100 mm	Form	Crosshead, Philips
Size	2		

Classifications

ETIM 6.0	EC000144	ETIM 7.0	EC000144
ETIM 8.0	EC000144	ECLASS 9.0	21-04-04-06
ECLASS 9.1	21-04-04-06	ECLASS 10.0	21-04-04-06
ECLASS 11.0	21-04-04-06	ECLASS 12.0	21-04-04-06

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[2749970000](#)