

SD EL 0.3X1.5X40 PICO**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



Slotted screwdriver with rounded blade SD DIN 5265,
ISO 2380/2, output to DIN 5264, ISO 2380/1.
ChromTop tip, SoftFinish grip

General ordering data

Version	Screwdriver, Blade width (B): 1.5 mm, Blade length: 40 mm, Blade thickness (A): 0.3 mm
Order No.	2750060000
Type	SD EL 0.3X1.5X40 PICO
GTIN (EAN)	4050118897548
Qty.	1 pc(s).

SD EL 0.3X1.5X40 PICO**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technical data**Dimensions and weights**

Width	140 mm	Width (inches)	5.512 inch
Net weight	20 g		

Screwing tools

Blade length	40 mm	Blade thickness (A)	0.3 mm
Blade width (B)	1.5 mm	Form	Slotted

Classifications

ETIM 6.0	EC000158	ETIM 7.0	EC000158
ETIM 8.0	EC000158	ECLASS 9.0	21-04-04-07
ECLASS 9.1	21-04-04-07	ECLASS 10.0	21-04-04-07
ECLASS 11.0	21-04-04-07	ECLASS 12.0	21-04-04-07

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[2750060000](#)