

CUTFIX PRO FEEDER**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

- For automatically cutting individual wires to length
- High repeat accuracy due to the precise servo DC drive
- Interface for controlling the automatic cutter via an IBM-compatible PC

General ordering data

Version	Automatic machines, Cutting machine
Order No.	2797200000
Type	CUTFIX PRO FEEDER
GTIN (EAN)	4064675213215
Qty.	1 pc(s).

CUTFIX PRO FEEDER

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	370 mm	Depth (inches)	14.567 inch
Height	250 mm	Height (inches)	9.842 inch
Width	300 mm	Width (inches)	11.811 inch
Net weight	13,000 g		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Automatic cutting

Amount pre-selection, max.	Adjustable part quantity code	Aperture (max. diameter)	8 mm outer diameter
Connected load	0.1 kW	Display	LCD display
Drive	electrical	Electrical connection	100 - 240 V AC / 50/60 Hz
Flexible/solid individual conductors	max. 10 mm ² / max. 2.5 mm ²	Keyboard	Touch display
Length pre-selection, max.	999,999 mm	Length pre-selection, min.	1 mm
Software	for data exchanging with IBM-compatible PC		

Classifications

ETIM 6.0	EC002778	ETIM 7.0	EC002778
ETIM 8.0	EC002778	ECLASS 9.0	17-13-01-01
ECLASS 9.1	17-13-01-03	ECLASS 10.0	17-13-01-03
ECLASS 11.0	17-13-01-01	ECLASS 12.0	17-13-01-01

Approvals

Approvals



ROHS

Conform

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[2797200000](#)