

RKDG D13 PT6**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

**Intelligent cabling solutions can save you valuable time and money.**

The FieldPower® modular system contains the right solution for every cabling task.

Foldable seals for the use of pre-assembled cables

Seals available with M16 and M20 connection thread

Integration of operating and signalling devices into the seal possible

General ordering data

Order No.	4323230000
Type	RKDG D13 PT6
GTIN (EAN)	4032248641239
Qty.	10 pc(s).

RKDG D13 PT6**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	18 mm	Depth (inches)	0.709 inch
Height	33.8 mm	Height (inches)	1.331 inch
Width	46.7 mm	Width (inches)	1.839 inch
Net weight	2.36 g		

Temperatures

Operating temperature -40 °C...85 °C

General data

Clamping range, max.	13 mm	Clamping range, min.	11 mm
Colour	black	Design	Foldable seal
Line type	round	Material	EPDM
Mounting position, installation notice	in FieldPower® sealing slot	Protection degree	IP65
Silicone	No	UL 94 flammability rating	HB

Classifications

ETIM 6.0	EC002624	ETIM 7.0	EC002624
ETIM 8.0	EC002624	ECLASS 9.1	27-18-27-90
ECLASS 10.0	27-18-28-15	ECLASS 11.0	27-18-28-15
ECLASS 12.0	27-18-28-15		

Approvals

ROHS Conform

Downloads

Approval/Certificate/Document of Conformity	UL Certificate FieldPower® Box and accessories Manufacturer's Declaration FieldPower® Enclosure parts
Engineering Data	CAD data – STEP
Engineering Data	EPLAN
Catalogues	Catalogues in PDF-format

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[4323230000](#)