

**PAC-CTLX-HE20-V0-3M****Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



Similar to illustration

The pre-assembled PAC cables establish an electrical and logical connection between the PLC and the PLC interfaces. These cables consist of the following components:

- Manufacturer's PLC connector.
- Multi-pole LiYY or LY YCY cable (shielded) with a cross-section of 0.14 mm<sup>2</sup> or 0.25 mm<sup>2</sup>.
- Flat cable connector, SUB-D or RSV, for connection to the interface.

The cables are tested automatically for their continuity and insulation to guarantee the functionality for which they have been designed.

**General ordering data**

|            |                                                            |
|------------|------------------------------------------------------------|
| Version    | Pre-assembled cable, PAC, Cable LiYY, 0.25 mm <sup>2</sup> |
| Order No.  | <a href="#">7789039030</a>                                 |
| Type       | PAC-CTLX-HE20-V0-3M                                        |
| GTIN (EAN) | 8430243957601                                              |
| Qty.       | 1 pc(s).                                                   |

**PAC-CTLX-HE20-V0-3M**

Weidmüller Interfaces GmbH &amp; Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

**Technical data****Dimensions and weights**

Net weight 442 g

**Temperatures**

Storage temperature -10...60 °C

Operating temperature -10...50 °C

**Environmental Product Compliance**

REACH SVHC

Lead 7439-92-1

SCIP

4bbf2c0d-0764-4fc8-bb24-9351c28c190d

**General Data**

|                    |                                      |                       |                              |
|--------------------|--------------------------------------|-----------------------|------------------------------|
| Cable              | Cable LiYY                           | Cable length          | 3 m                          |
| Connector PLC side | ROCKWELL CONTROL LOGIX 1756-TBNH 20P | Interface connector   | FLAT CABLE CONECTOR HE10 20P |
| Material           | PVC                                  | Number of poles, min. | 20-pole                      |
| Outer diameter     | 8.6 ± 1 mm                           | Suitable for          | Digital signals              |
| Wire cross-section | 0.25 mm <sup>2</sup>                 |                       |                              |

**Electrical Data**

|                        |                   |                                             |           |
|------------------------|-------------------|---------------------------------------------|-----------|
| Capacity wire / shield | 300 pF/m          | Capacity wire / wires                       | 300 pF/m  |
| High voltage test      | 1 kV/1s           | Permissible current strength per path, max. | 1 A       |
| Rated voltage          | ≤ 60 Vdc ≤ 25 Vac | Resistance                                  | ≤ 80 mΩ/m |
| Total current, max.    | 3 A               |                                             |           |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000237    | ETIM 7.0    | EC000237    |
| ETIM 8.0    | EC000237    | ECLASS 9.0  | 27-24-22-20 |
| ECLASS 9.1  | 27-24-22-20 | ECLASS 10.0 | 27-24-22-20 |
| ECLASS 11.0 | 27-24-22-20 | ECLASS 12.0 | 27-24-22-20 |

**Approvals**

Approvals



ROHS

Conform

**Downloads**Catalogues [Catalogues in PDF-format](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[7789039030](#)