

**PAC-UNIV-HE10-LCF-1M5****Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



Similar to illustration

**General ordering data**

|            |                                                            |
|------------|------------------------------------------------------------|
| Version    | Pre-assembled cable, PAC, Cable LiYY, 0.14 mm <sup>2</sup> |
| Order No.  | <a href="#">7789101015</a>                                 |
| Type       | PAC-UNIV-HE10-LCF-1M5                                      |
| GTIN (EAN) | 4032248112319                                              |
| Qty.       | 1 pc(s).                                                   |

**PAC-UNIV-HE10-LCF-1M5****Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

**Technical data****Dimensions and weights**

Net weight 63.3 g

**Temperatures**

Storage temperature -10...60 °C

Operating temperature -10...50 °C

**General Data**

|                    |                                          |                       |                              |
|--------------------|------------------------------------------|-----------------------|------------------------------|
| Cable              | Cable LiYY                               | Cable length          | 1.5 m                        |
| Connector PLC side | H0.14/10 (FERRULES 0.14mm <sup>2</sup> ) | Interface connector   | FLAT CABLE CONECTOR HE10 10P |
| Material           | PVC                                      | Number of poles, min. | 10-pole                      |
| Outer diameter     | 7 ± 1 mm                                 | Suitable for          | Digital signals              |
| Wire cross-section | 0.14 mm <sup>2</sup>                     |                       |                              |

**Electrical Data**

|                        |                   |                                             |            |
|------------------------|-------------------|---------------------------------------------|------------|
| Capacity wire / shield | 300 pF/m          | Capacity wire / wires                       | 300 pF/m   |
| High voltage test      | 1 KV/1s           | Permissible current strength per path, max. | 1 A        |
| Rated voltage          | ≤ 60 Vdc ≤ 25 Vac | Resistance                                  | ≤ 150 mΩ/m |
| Total current, max.    | 3 A               |                                             |            |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000237    | ETIM 7.0    | EC000237    |
| ETIM 8.0    | EC000237    | ECLASS 9.0  | 27-24-22-20 |
| ECLASS 9.1  | 27-24-22-20 | ECLASS 10.0 | 27-24-22-20 |
| ECLASS 11.0 | 27-24-22-20 | ECLASS 12.0 | 27-24-22-20 |

**Approvals**

ROHS Conform

**Downloads**

User Documentation [Colours chart](#)

Catalogues [Catalogues in PDF-format](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[7789101015](#)