

SCHUKO TS35**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

- Simple installation in electrical cabinet
- TS35 module can be mounted on rail
- VDE mark of conformity
- Two-pole with earthing contact

General ordering data

Version	Electrical-cabinet socket outlet TS 35
Order No.	8734580000
Type	SCHUKO TS35
GTIN (EAN)	4032248407835
Qty.	10 pc(s).

SCHUKO TS35

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Height	45 mm	Height (inches)	1.772 inch
Width	76 mm	Width (inches)	2.992 inch
Length	60 mm	Length (inches)	2.362 inch
Net weight	95 g		

Temperatures

Storage temperature	-20 °C...40 °C	Operating temperature	-20 °C...40 °C
---------------------	----------------	-----------------------	----------------

Input

Rated current	16 A
---------------	------

General data

Colour	beige	Design	Installation housing
Rail	TS 35		

Insulation coordination

Pollution severity	2	Surge voltage category	II
--------------------	---	------------------------	----

Insulation coordination acc. to EN 50178

Pollution severity	2	Surge voltage category	II
--------------------	---	------------------------	----

Classifications

ETIM 6.0	EC000125	ETIM 7.0	EC000125
ETIM 8.0	EC000125	ECLASS 9.0	27-14-40-42
ECLASS 9.1	27-14-40-42	ECLASS 10.0	27-14-40-42
ECLASS 11.0	27-14-40-42	ECLASS 12.0	27-14-40-42

Approvals

Approvals



ROHS

Conform

Downloads

Approval/Certificate/Document of
Conformity[Declaration of Conformity](#)

Catalogues

[Catalogues in PDF-format](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[8734580000](#)