

**DMS 3 SET 1****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Weidmüller torque screwdrivers have an ergonomic design and are therefore ideal for use with one hand. They can be used without causing fatigue in all installation positions. Apart from that, they incorporate an automatic torque limiter and have a good reproducibility accuracy.

**General ordering data**

|            |                                          |
|------------|------------------------------------------|
| Version    | DMS 3, Mains-operated torque screwdriver |
| Order No.  | <a href="#">9007470000</a>               |
| Type       | DMS 3 SET 1                              |
| GTIN (EAN) | 4008190299224                            |
| Qty.       | 1 pc(s).                                 |

**DMS 3 SET 1****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

|            |         |                |             |
|------------|---------|----------------|-------------|
| Depth      | 205 mm  | Depth (inches) | 8.071 inch  |
| Width      | 325 mm  | Width (inches) | 12.795 inch |
| Net weight | 1,770 g |                |             |

**Environmental Product Compliance**

|            |                |
|------------|----------------|
| REACH SVHC | Lead 7439-92-1 |
|------------|----------------|

**Technical data**

|                        |                                                                                          |
|------------------------|------------------------------------------------------------------------------------------|
| Description of article | Cordless torque screwdriver set, incl. rechargeable battery, charger, bits, plastic case |
|------------------------|------------------------------------------------------------------------------------------|

**Electric screwdriver**

|                                |                              |                      |                         |
|--------------------------------|------------------------------|----------------------|-------------------------|
| Battery voltage                | 2.4 V                        | Bit holder           | 1/4" DIN 3126 Form E6.3 |
| Idling speed                   | 200 u. 400 min <sup>-1</sup> | Rated voltage        | 2.4 V                   |
| Rechargeable batteries         | Ni-Mh cells                  | Torque setting, max. | 3 Nm                    |
| Torque setting, min.           | 0.3 Nm                       | Weight               | 2,004 g                 |
| Weight of rechargeable battery | 122 g                        |                      |                         |

**Screwing tools**

|                      |      |                      |        |
|----------------------|------|----------------------|--------|
| Torque setting, max. | 3 Nm | Torque setting, min. | 0.3 Nm |
|----------------------|------|----------------------|--------|

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001395    | ETIM 7.0    | EC001395    |
| ETIM 8.0    | EC001395    | ECLASS 9.0  | 21-05-21-90 |
| ECLASS 9.1  | 21-04-04-17 | ECLASS 10.0 | 21-05-21-90 |
| ECLASS 11.0 | 21-05-08-90 | ECLASS 12.0 | 21-05-08-90 |

**Approvals**

Approvals



ROHS

Conform

**Downloads**

|                  |                                          |
|------------------|------------------------------------------|
| Engineering Data | <a href="#">WSCAD</a>                    |
| Catalogues       | <a href="#">Catalogues in PDF-format</a> |

### DMS 3 SET 1

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

### Example of use



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[9007470000](#)