

CRIMPER 25 N D4**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Crimping tools for non-insulated connectors**

Rolled cable lugs, tubular cable lugs, terminal pins, parallel and serial connectors

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

General ordering data

Version	Tools, Crimping tool for contacts, 10mm ² , 25mm ²
Order No.	9040460000
Type	CRIMPER 25 N D4
GTIN (EAN)	4008190461508
Qty.	1 pc(s).

CRIMPER 25 N D4**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Width	250 mm	Width (inches)	9.842 inch
Net weight	550 g		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Technical data

Description of article	Crimping tool for non-insulated connectors, 10-25 mm ²	Version	Mechanical, without interchangeable inserts
------------------------	---	---------	---

Description of contact

Crimping range, max.	25 mm ²	Crimping range, min.	10 mm ²
Type of contact	Uninsulated connection		

tool data crimping

Crimping profile 1, max.	10 mm ²	Crimping profile 2, max.	16 mm ²
Crimping profile 3, max.	25 mm ²		

Classifications

ETIM 6.0	EC000168	ETIM 7.0	EC000168
ETIM 8.0	EC000168	ECLASS 9.0	21-04-38-11
ECLASS 9.1	21-04-38-11	ECLASS 10.0	21-04-38-11
ECLASS 11.0	21-04-38-11	ECLASS 12.0	21-04-38-11

Approvals

Approvals

**Downloads**

Catalogues	Catalogues in PDF-format
------------	--

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[9040460000](#)