

VG 16-SS 68 KB 10-14**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

General ordering data

Version	VG S (standard stainless steel cable gland), Cable glands, PG 16, 6.5 mm, OD min. 10 - OD max. 14 mm, Stainless steel 1.4305 (303)
Order No.	1009780000
Type	VG 16-SS 68 KB 10-14
GTIN (EAN)	4032248714506
Qty.	25 pc(s).

VG 16-SS 68 KB 10-14

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Length	34 mm	Length (inches)	1.339 inch
Net weight	31.2 g		

Temperatures

Operating temperature	-40 °C... 100 °C
-----------------------	------------------

General information

AF size 1	24 mm	AF size 2	24 mm
Cable glands	PG	External thread	PG 16
Halogen	Yes	Length of thread	6.5 mm
Material	Stainless steel 1.4305 (303)	O-Ring	NBR
Operating temperature range, max.	100 °C	Operating temperature range, min.	-40 °C
Outer cable diameter, max.	14 mm	Outer cable diameter, min.	10 mm
Protection degree	IP54, IP66, IP67, IP68 - 5 bar (30 min.), IP69K	Seal insert	CR
Sealing	NBR	Tightening torque	7 Nm
Torque for cap nut, max.	11.5 Nm	Torque for cap nut, min.	10.5 Nm
Torque for connecting adapter, max.	7.5 Nm	Torque for connecting adapter, min.	6.5 Nm

Classifications

ETIM 6.0	EC000441	ETIM 7.0	EC000441
ETIM 8.0	EC000441	ECLASS 9.0	27-14-44-32
ECLASS 9.1	27-14-44-32	ECLASS 10.0	27-14-44-32
ECLASS 11.0	27-14-44-32		

Approvals

Approvals



ROHS

Conform

Downloads

Engineering Data	CAD data – STEP
Engineering Data	EPLAN, WSCAD
Catalogues	Catalogues in PDF-format
Brochures	

VG 16-SS 68 KB 10-14**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Brass lock nuts, nickel-plated**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	SKMU PG16-MS	Version
Order No.	1694110000	SKMU MS (brass locknut), Locknut, PG 16, 3 mm, Brass, nickel-plated
GTIN (EAN)	4008190872274	
Qty.	100 pc(s).	

Neoprene flat gasket - GWDR NP

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	GWDR PG16-NP	Version
Order No.	1719580000	GWDR NP (flat gasket - neoprene), Sealing ring, PG 16, Neoprene
GTIN (EAN)	4008190352844	
Qty.	100 pc(s).	

VG 16-SS 68 KB 10-14**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Polyethylene flat gasket - GWDR PO**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	GWDR PG16-PO	Version
Order No.	1719480000	GWDR PO (flat gasket - polyethylene), Sealing ring, PG 16,
GTIN (EAN)	4008190352745	Polyethylene
Qty.	100 pc(s).	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1009780000](#)