

WQV 10/3**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

General ordering data

Version	W-Series, Cross-connector, For the terminals, Number of poles: 3
Order No.	1054960000
Type	WQV 10/3
GTIN (EAN)	4008190079079
Qty.	50 pc(s).

WQV 10/3

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	18 mm	Depth (inches)	0.709 inch
Height	26.8 mm	Height (inches)	1.055 inch
Width	7.55 mm	Width (inches)	0.297 inch
Net weight	5.5 g		

Temperatures

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-60 °C
Continuous operating temp., max.	130 °C		

Material data

Material	PA 66	Colour	yellow
UL 94 flammability rating	V-0		

System specifications

Version	For the terminals
---------	-------------------

Additional technical data

Installation advice	Direct mounting	Type of fixing	when screwed in
---------------------	-----------------	----------------	-----------------

Cross-connector

Number of cross-connected terminals	3	Rated current, multi-pole	57 A
Tightening torque range for fixing screw	0.5...1.0 Nm	Type	Cross-connector

Dimensions

Pitch in mm (P)	9.9 mm
-----------------	--------

General

Installation advice	Direct mounting	Number of poles	3
---------------------	-----------------	-----------------	---

Rating data

Rated current	63 A
---------------	------

Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ECLASS 9.0	27-14-11-40
ECLASS 9.1	27-14-11-40	ECLASS 10.0	27-14-11-40
ECLASS 11.0	27-14-11-40	ECLASS 12.0	27-14-11-40

Approvals

Approvals



ROHS

Conform

Creation date September 15, 2022 10:38:14 PM CEST

Catalogue status 09.09.2022 / We reserve the right to make technical changes.

WQV 10/3

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

Approval/Certificate/Document of
Conformity

[EAC certificate](#)

Engineering Data

[CAD data – 08873_WQV_10-3_DXF.dxf](#)

[CAD data – STEP](#)

Engineering Data

[EPLAN, WSCAD, Zuken E3.S](#)

User Documentation

[Beipackzettel_WQV.pdf](#)

[StorageConditionsTerminalBlocks](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1054960000](#)