

## WZAD120

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

### Product image



### General ordering data

|            |                                 |
|------------|---------------------------------|
| Version    | W-Series, Additional connection |
| Order No.  | <a href="#">1066 100000</a>     |
| Type       | WZAD120                         |
| GTIN (EAN) | 4008 1900 17019                 |
| Qty.       | 10 pc(s).                       |

**WZAD120****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

|            |          |                 |            |
|------------|----------|-----------------|------------|
| Depth      | 10 mm    | Depth (inches)  | 0.394 inch |
| Height     | 44.41 mm | Height (inches) | 1.748 inch |
| Width      | 24 mm    | Width (inches)  | 0.945 inch |
| Net weight | 7.6 g    |                 |            |

**Temperatures**

|                                  |                |                                  |        |
|----------------------------------|----------------|----------------------------------|--------|
| Storage temperature              | -25 °C...55 °C | Continuous operating temp., min. | -50 °C |
| Continuous operating temp., max. | 120 °C         |                                  |        |

**Material data**

|          |               |        |             |
|----------|---------------|--------|-------------|
| Material | tinned copper | Colour | Silver grey |
|----------|---------------|--------|-------------|

**System specifications**

|                                     |                       |                  |   |
|-------------------------------------|-----------------------|------------------|---|
| Version                             | Additional connection | Number of levels | 1 |
| Number of clamping points per level | 1                     |                  |   |

**Conductors for clamping (rated connection)**

|                       |   |
|-----------------------|---|
| Number of connections | 1 |
|-----------------------|---|

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002848    | ETIM 7.0    | EC002848    |
| ETIM 8.0    | EC002848    | ECLASS 9.0  | 27-14-11-92 |
| ECLASS 9.1  | 27-14-11-92 | ECLASS 10.0 | 27-14-11-92 |
| ECLASS 11.0 | 27-14-11-92 |             |             |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|                    |                                                 |
|--------------------|-------------------------------------------------|
| Engineering Data   | <a href="#">CAD data – STEP</a>                 |
| Engineering Data   | <a href="#">EPLAN, WSCAD, Zuken E3.S</a>        |
| User Documentation | <a href="#">StorageConditionsTerminalBlocks</a> |
| Catalogues         | <a href="#">Catalogues in PDF-format</a>        |
| Brochures          |                                                 |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1066100000](#)