

ETA 1170 21 15A**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Similar to illustration

Weidmueller offer circuit breakers for the integration of our fuse terminals for automotive fuses with a range from 100 mA to 25 A.

General ordering data

Version	Accessories, Circuit breaker, 15 A
Order No.	1278810000
Type	ETA 1170 21 15A
GTIN (EAN)	4050118091328
Qty.	5 pc(s).

ETA 1170 21 15A

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	51.6 mm	Depth (inches)	2.031 inch
Height	22 mm	Height (inches)	0.866 inch
Width	9.8 mm	Width (inches)	0.386 inch
Net weight	10.4 g		

Temperatures

Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	120 °C
----------------------------------	--------	----------------------------------	--------

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Material data

Colour	black
--------	-------

System specifications

Version	Fuse cartridge
---------	----------------

Additional technical data

Installation advice	Direct mounting	Type of mounting	Plugged
---------------------	-----------------	------------------	---------

Fuse cartridges

Colour	black	Current	15 A
Version	Fuse cartridge		

General

Installation advice	Direct mounting
---------------------	-----------------

Rating data

Rated voltage	28 V DC	Rated current	15 A
---------------	---------	---------------	------

Classifications

ETIM 6.0	EC000035	ETIM 7.0	EC000035
ETIM 8.0	EC002704	ECLASS 9.0	27-14-20-01
ECLASS 9.1	27-14-20-01	ECLASS 10.0	27-14-20-01
ECLASS 11.0	27-14-20-01		

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN, WSCAD
User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1278810000](#)