

**PAC-S300-SD37-V5-1M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration

The pre-assembled PAC cables establish an electrical and logical connection between the PLC and the PLC interfaces. These cables consist of the following components:

- Manufacturer's PLC connector.
- Multi-pole LIYY or LY YCY cable (shielded) with a cross-section of 0.14 mm<sup>2</sup> or 0.25 mm<sup>2</sup>.
- Flat cable connector, SUB-D or RSV, for connection to the interface.

The cables are tested automatically for their continuity and insulation to guarantee the functionality for which they have been designed.

**General ordering data**

|                 |                                                             |
|-----------------|-------------------------------------------------------------|
| Version         | Pre-assembled cable, PAC, Cable LiYCY, 0.25 mm <sup>2</sup> |
| Order No.       | <a href="#">1345040010</a>                                  |
| Type            | PAC-S300-SD37-V5-1M                                         |
| GTIN (EAN)      | 4032248142316                                               |
| Qty.            | 1 pc(s).                                                    |
| Available until | 2014-05-20                                                  |

Creation date September 16, 2022 3:57:18 AM CEST

**PAC-S300-SD37-V5-1M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

|            |       |
|------------|-------|
| Net weight | 374 g |
|------------|-------|

**Temperatures**

|                     |             |                       |             |
|---------------------|-------------|-----------------------|-------------|
| Storage temperature | -10...60 °C | Operating temperature | -10...50 °C |
|---------------------|-------------|-----------------------|-------------|

**Environmental Product Compliance**

|            |                |      |                                      |
|------------|----------------|------|--------------------------------------|
| REACH SVHC | Lead 7439-92-1 | SCIP | 4bbf2c0d-0764-4fc8-bb24-9351c28c190d |
|------------|----------------|------|--------------------------------------|

**General Data**

|                    |                                 |                       |                  |
|--------------------|---------------------------------|-----------------------|------------------|
| Cable              | Cable LiYCY                     | Cable length          | 1 m              |
| Connector PLC side | S7300 40P<br>6ES7392-1BM01-0AA0 | Interface connector   | SUB-D FEMALE 37P |
| Material           | PVC                             | Number of poles, min. | 37-pole          |
| Outer diameter     | 12.2 ± 1 mm                     | Suitable for          | Analogue signals |
| Wire cross-section | 0.25 mm <sup>2</sup>            |                       |                  |

**Electrical Data**

|                        |                   |                                             |           |
|------------------------|-------------------|---------------------------------------------|-----------|
| Capacity wire / shield | 300 pF/m          | Capacity wire / wires                       | 300 pF/m  |
| High voltage test      | 1 kV/1s           | Permissible current strength per path, max. | 1 A       |
| Rated voltage          | ≤ 60 Vdc ≤ 25 Vac | Resistance                                  | ≤ 80 mΩ/m |
| Total current, max.    | 3 A               |                                             |           |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000237    | ETIM 7.0    | EC000237    |
| ETIM 8.0    | EC000237    | ECLASS 9.0  | 27-24-22-20 |
| ECLASS 9.1  | 27-24-22-20 | ECLASS 10.0 | 27-24-22-20 |
| ECLASS 11.0 | 27-24-22-20 | ECLASS 12.0 | 27-24-22-20 |

**Approvals**

Approvals



|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|            |                                          |
|------------|------------------------------------------|
| Catalogues | <a href="#">Catalogues in PDF-format</a> |
|------------|------------------------------------------|

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1345040010](#)