

**PAC-UNIV-D37F-D37F-3M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration

**General ordering data**

|                 |                                                    |
|-----------------|----------------------------------------------------|
| Version         | Pre-assembled cable, PAC, Cable LiYCY, 12.2 ± 1 mm |
| Order No.       | <a href="#">1349930030</a>                         |
| Type            | PAC-UNIV-D37F-D37F-3M                              |
| GTIN (EAN)      | 4032248190256                                      |
| Qty.            | 1 pc(s).                                           |
| Available until | 2014-05-20                                         |

## PAC-UNIV-D37F-D37F-3M

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |       |
|------------|-------|
| Net weight | 877 g |
|------------|-------|

## Temperatures

|                     |             |                       |             |
|---------------------|-------------|-----------------------|-------------|
| Storage temperature | -10...60 °C | Operating temperature | -10...50 °C |
|---------------------|-------------|-----------------------|-------------|

## General Data

|                    |                      |                       |                  |
|--------------------|----------------------|-----------------------|------------------|
| Cable              | Cable LiYCY          | Cable length          | 3 m              |
| Connector PLC side | SUB-D FEMALE 37P     | Interface connector   | SUB-D FEMALE 37P |
| Material           | PVC                  | Number of poles, min. | 37-pole          |
| Outer diameter     | 12.2 ± 1 mm          | Suitable for          | Analogue signals |
| Wire cross-section | 0.25 mm <sup>2</sup> |                       |                  |

## Electrical Data

|                        |                     |                                             |           |
|------------------------|---------------------|---------------------------------------------|-----------|
| Capacity wire / shield | 300 pF/m            | Capacity wire / wires                       | 300 pF/m  |
| Operating voltage      | ≤ 60 V DC ≤ 25 V AC | Permissible current strength per path, max. | 1 A       |
| Rated voltage          | ≤ 60 Vdc ≤ 25 Vac   | Resistance                                  | ≤ 80 mΩ/m |
| Total current, max.    | 3 A                 |                                             |           |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000237    | ETIM 7.0    | EC000237    |
| ETIM 8.0    | EC000237    | ECLASS 9.0  | 27-24-22-20 |
| ECLASS 9.1  | 27-24-22-20 | ECLASS 10.0 | 27-24-22-20 |
| ECLASS 11.0 | 27-24-22-20 | ECLASS 12.0 | 27-24-22-20 |

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Downloads

|            |                                          |
|------------|------------------------------------------|
| Catalogues | <a href="#">Catalogues in PDF-format</a> |
|------------|------------------------------------------|

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1349930030](#)