

SAI-WDF-3P-M8

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



General ordering data

Order No.	1392390000
Type	SAI-WDF-3P-M8
GTIN (EAN)	4050118192766
Qty.	1 pc(s).

SAI-WDF-3P-M8

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	21 g
------------	------

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Technical data customisable plug-in connectors

Coding	M8 = none	Contact surface	Gold-plated
Housing main material	CuZn	Number of poles	3
Protection degree	IP67	Rated current	4 A
Rated voltage	30 V	Temperature range of housing	-40 ... +85 °C

General technical specifications

Coding	M8 = none	Connection thread	M8 socket, M8 pin
Contact material	CuZn	Contact surface	Gold-plated
Housing main material	CuZn	Number of poles	3
Protection degree	IP67	Rated current	4 A
Rated voltage	30 V	Temperature range of housing	-40 ... +85 °C

Classifications

ETIM 6.0	EC002925	ETIM 7.0	EC002925
ETIM 8.0	EC002925	ECLASS 9.0	27-44-01-06
ECLASS 9.1	27-44-01-06	ECLASS 10.0	27-44-01-06
ECLASS 11.0	27-44-01-06		

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN


Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

Wiring diagram



Pole scheme



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1392390000](#)