

**IE-FM5Z2LO0010MSD0SD0-X****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Assembled IE cables, FO

**General ordering data**

|            |                                                                                        |
|------------|----------------------------------------------------------------------------------------|
| Version    | Patch cable, duplex clip included, SC duplex IP 20, SC duplex IP 20, 50 µm, LSZH, 10 m |
| Order No.  | <a href="#">1433970100</a>                                                             |
| Type       | IE-FM5Z2LO0010MSD0SD0-X                                                                |
| GTIN (EAN) | 4050118242591                                                                          |
| Qty.       | 1 pc(s).                                                                               |

Creation date September 16, 2022 5:17:48 AM CEST

Catalogue status 09.09.2022 / We reserve the right to make technical changes.

## IE-FM5Z2LO0010MSD0SD0-X

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |       |                 |              |
|------------|-------|-----------------|--------------|
| Length     | 10 m  | Length (inches) | 393.701 inch |
| Net weight | 100 g |                 |              |

## Temperatures

|                       |                |
|-----------------------|----------------|
| Operating temperature | -20 °C...70 °C |
|-----------------------|----------------|

## Cable specific standards

|                                                                  |             |                                                         |                               |
|------------------------------------------------------------------|-------------|---------------------------------------------------------|-------------------------------|
| Specification for checking the symmetrical communication cabling | IEC 61935-3 | Specification for twisted-pair device connection cables | IEC 61156-6, DIN EN 50288-4-2 |
|------------------------------------------------------------------|-------------|---------------------------------------------------------|-------------------------------|

## Standards

|                    |             |
|--------------------|-------------|
| Connector standard | IEC 61754-4 |
|--------------------|-------------|

## Fibre-optic

|             |                                                  |           |                                                    |
|-------------|--------------------------------------------------|-----------|----------------------------------------------------|
| Attenuation | ≤ 2.7 dB/km at 850 nm,<br>≤ 0.8 dB/km at 1300 nm | Bandwidth | ≥ 600 MHz*km at 850 nm,<br>≥ 600 MHz*km at 1300 nm |
| Fibre type  | GOF, Multimode, OM2                              |           |                                                    |

## Cable structure

|                       |              |                  |        |
|-----------------------|--------------|------------------|--------|
| Cable layout          | ZIPCORD      | Core diameter    | 50 µm  |
| Material sheath       | LSZH         | Primary coating  | 245 µm |
| Sheath diameter       | 2.8 * 5.7 mm | Sheathing colour | orange |
| Standard designations | I-V(ZN)H     |                  |        |

## Mechanical and material properties of cable

|                                 |       |                                |             |
|---------------------------------|-------|--------------------------------|-------------|
| Halogen                         | No    | Min. bending radius, once only | 28 mm       |
| Min. bending radius, repetitive | 56 mm | Resistance to spread of flame  | IEC 60754-2 |

## Plug

|           |                                                                    |            |                                                                    |
|-----------|--------------------------------------------------------------------|------------|--------------------------------------------------------------------|
| Plug left | SC-Duplex, IP20, male contact, straight, plug, Plastic, unshielded | Plug right | SC-Duplex, IP20, male contact, straight, plug, Plastic, unshielded |
|-----------|--------------------------------------------------------------------|------------|--------------------------------------------------------------------|

## Plug, left

|                |                 |
|----------------|-----------------|
| Connector left | SC duplex IP 20 |
|----------------|-----------------|

## Plug, right

|                 |                 |
|-----------------|-----------------|
| Connector right | SC duplex IP 20 |
|-----------------|-----------------|

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002607    | ETIM 7.0    | EC002607    |
| ETIM 8.0    | EC002607    | ECLASS 9.0  | 27-06-10-03 |
| ECLASS 9.1  | 27-06-10-03 | ECLASS 10.0 | 27-06-10-03 |
| ECLASS 11.0 | 27-06-10-03 | ECLASS 12.0 | 27-06-10-03 |

Creation date September 16, 2022 5:17:48 AM CEST

## IE-FM5Z2LO0010MSD0SD0-X

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Downloads

|                    |                                                                                                                       |
|--------------------|-----------------------------------------------------------------------------------------------------------------------|
| User Documentation | <a href="#">MAN IE GUIDE DE</a><br><a href="#">MAN IE GUIDE EN</a>                                                    |
| Catalogues         | <a href="#">Catalogues in PDF-format</a>                                                                              |
| Brochures          | <a href="#">FL FIELDWIRING EN</a><br><a href="#">PI PROFINET CABLING EN</a><br><a href="#">PI PROFINET CABLING EN</a> |

**IE-FM5Z2LO0010MSD0SD0-X**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

### Detailed drawing



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1433970100](#)