

CP DC UPS TF25**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Due to the wide range of variants with output voltages of 5, 12, 24, and 48 V and extensive international approvals, they are suitable for use in many applications. The power range extends from 35 W to 350 W. The individual adaptability makes PRO-PM the right choice for many standard machines.

General ordering data

Version	
Order No.	1444540000
Type	CP DC UPS TF25
GTIN (EAN)	4050118249880
Qty.	1 pc(s).

CP DC UPS TF25**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Net weight	142 g
------------	-------

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Classifications

ETIM 6.0	EC001578	ETIM 7.0	EC003250
ETIM 8.0	EC003250	ECLASS 9.0	27-06-20-11
ECLASS 9.1	27-06-90-90	ECLASS 10.0	27-06-01-06
ECLASS 11.0	27-06-01-06	ECLASS 12.0	27-06-01-06

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

User Documentation	Operating instruction
Catalogues	Catalogues in PDF-format

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1444540000](#)