

KQI-M2/-1**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Insulated cable connector in PVC or PC/PA**

- Conventional designs
- Not soldered
- With conical entry funnel, except for joint connector

General ordering data

Version	cable lug, terminal end, Insulated cable connector, 1 mm ² , 0.5 mm ² - 1 mm ²
Order No.	1492140000
Type	KQI-M2/-1
GTIN (EAN)	4050118302127
Qty.	100 pc(s).

KQI-M2/-1**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight	0.72 g
------------	--------

Connectors

Conductor cross-section	1 mm ²	Conductor cross-section, max.	1 mm ²
Conductor cross-section, min.	0.5 mm ²	Connection length (l)	17 mm
Hole	M 2	Identification colour	red
Inside diameter of collar (d4)	4 mm	Inside diameter of flange (d2)	2.2 mm
Inside diameter of shaft (d1)	1.6 mm	Insulation	Available
Material/plastic	PC	Outside diameter of shaft (d3)	6 mm

Classifications

ETIM 6.0	EC001059	ETIM 7.0	EC001059
ETIM 8.0	EC001059	ECLASS 9.0	27-40-02-12
ECLASS 9.1	27-40-02-12	ECLASS 10.0	27-40-02-12
ECLASS 11.0	27-40-02-12	ECLASS 12.0	27-40-02-12

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN
Catalogues	Catalogues in PDF-format
Brochures	

KQI-M2/-1

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1492140000](#)