

KQI-M6/-2,5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Insulated cable connector in PVC or PC/PA**

- Conventional designs
- Not soldered
- With conical entry funnel, except for joint connector

General ordering data

Version	cable lug, terminal end, Insulated cable connector, 2.5 mm ² , 1.5 mm ² - 2.5 mm ²
Order No.	1492320000
Type	KQI-M6/-2,5
GTIN (EAN)	4050118302417
Qty.	100 pc(s).

KQI-M6/-2,5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight	1.18 g
------------	--------

Connectors

Conductor cross-section	2.5 mm ²	Conductor cross-section, max.	2.5 mm ²
Conductor cross-section, min.	1.5 mm ²	Connection length (l)	22 mm
Hole	M 6	Identification colour	blue
Inside diameter of collar (d4)	4.4 mm	Inside diameter of flange (d2)	6.5 mm
Inside diameter of shaft (d1)	2.3 mm	Insulation	Available
Material/plastic	PC	Outside diameter of shaft (d3)	11 mm

Classifications

ETIM 6.0	EC001059	ETIM 7.0	EC001059
ETIM 8.0	EC001059	ECLASS 9.0	27-40-02-12
ECLASS 9.1	27-40-02-12	ECLASS 10.0	27-40-02-12
ECLASS 11.0	27-40-02-12	ECLASS 12.0	27-40-02-12

Approvals

ROHS	Conform
------	---------

Downloads


Engineering Data	EPLAN
Catalogues	Catalogues in PDF-format
Brochures	

KQI-M6/-2,5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1492320000](#)