


CLI C 02-3 RT/WS + CD**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm² to max. 70 mm². The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

General ordering data

Version	CableLine, Conductor and cable markers, 1.3 - 3 mm, 3 x 3.4 mm, red
Order No.	1568241737
Type	CLI C 02-3 RT/WS + CD
GTIN (EAN)	4008 190099640
Qty.	500 pc(s).

CLI C 02-3 RT/WS + CD

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	3.5 mm	Depth (inches)	0.138 inch
Height	3 mm	Height (inches)	0.118 inch
Width	3.4 mm	Width (inches)	0.134 inch
Net weight	0.06 g		

Temperatures

Operating temperature range	-30...80 °C
-----------------------------	-------------

General data

Colour	red	Colour of printing	white
Halogen	Yes	Insulation cross-section, max.	3
Material	PVC, soft, without Cadmium	Material colour according to resistance code	2
Number of markers per combination	1 Reel = Conductor and cable markers	Operating temperature range	-30...80 °C
Operating temperature range, max.	80 °C	Operating temperature range, min.	-30 °C
Orientation of print	horizontal	Printed characters	Symbols
Printing	+	Printing method	hot-embossing
Recommended industries	Process, Machinery	Type of printing	Standard
UL 94 flammability rating	V-0	Version	CD
Width	3.4 mm		

Conductor and cable markers

Conductor O.D.	1.3 - 3 mm	Conductor O.D., max.	3 mm
Conductor O.D., min.	1.3 mm	Conductor cross-section, max.	1.5 mm ²
Conductor cross-section, min.	0.2 mm ²	Cross-section for connected wire	0.2 - 1.5 mm ²
Halogen	Yes		

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ECLASS 9.0	27-40-04-01
ECLASS 9.1	27-40-04-01	ECLASS 10.0	27-40-04-01
ECLASS 11.0	27-28-11-02		

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN, WSCAD
Product Change Notification	PCN CableLine_DE PCN CableLine_EN
Catalogues	Catalogues in PDF-format

CLI C 02-3 RT/WS + CD

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Others



The CableLine range of wire and cable marker products provides users with solutions for the most diverse applications. The range of applications extends from narrow wires right up to cables with large outside diameters.

General ordering data

Type	CLI R 02-3 BL/WS -	Version
Order No.	0560001741	CableLine, Mounting mandrel
GTIN (EAN)	4008190990107	
Qty.	10 pc(s).	
Type	CLI R 02-3 RT/WS +	Version
Order No.	0560001739	CableLine, Mounting mandrel
GTIN (EAN)	4008190990145	
Qty.	10 pc(s).	

0 - 9



The CableLine range of wire and cable marker products provides users with solutions for the most diverse applications. The range of applications extends from narrow wires right up to cables with large outside diameters.

General ordering data

Type	CLI R 02-3 GE/SW 3	Version
Order No.	0560001510	CableLine, Mounting mandrel
GTIN (EAN)	4008190046941	
Qty.	10 pc(s).	
Type	CLI R 02-3 GE/SW 1	Version
Order No.	0560001504	CableLine, Mounting mandrel
GTIN (EAN)	4008190046590	
Qty.	10 pc(s).	
Type	CLI R 02-3 GE/SW 0	Version
Order No.	0560001501	CableLine, Mounting mandrel
GTIN (EAN)	4008190063498	
Qty.	10 pc(s).	
Type	CLI R 02-3 GE/SW 6	Version
Order No.	0560001519	CableLine, Mounting mandrel
GTIN (EAN)	4008190019129	
Qty.	10 pc(s).	

CLI C 02-3 RT/WS + CD

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Type	CLI R 02-3 GE/SW 8	Version
Order No.	0560001525	CableLine, Mounting mandrel
GTIN (EAN)	4008190154875	
Qty.	10 pc(s).	
Type	CLI R 02-3 GE/SW 4	Version
Order No.	0560001513	CableLine, Mounting mandrel
GTIN (EAN)	4008190186081	
Qty.	10 pc(s).	
Type	CLI R 02-3 GE/SW 2	Version
Order No.	0560001507	CableLine, Mounting mandrel
GTIN (EAN)	4008190083137	
Qty.	10 pc(s).	
Type	CLI R 02-3 GE/SW 5	Version
Order No.	0560001516	CableLine, Mounting mandrel
GTIN (EAN)	4008190188436	
Qty.	10 pc(s).	
Type	CLI R 02-3 GE/SW 7	Version
Order No.	0560001522	CableLine, Mounting mandrel
GTIN (EAN)	4008190185213	
Qty.	10 pc(s).	
Type	CLI R 02-3 GE/SW 9	Version
Order No.	0560001528	CableLine, Mounting mandrel
GTIN (EAN)	4008190141516	
Qty.	10 pc(s).	

Mandrels single



The CableLine range of wire and cable marker products provides users with solutions for the most diverse applications. The range of applications extends from narrow wires right up to cables with large outside diameters.

General ordering data

Type	CLI R 02 F, CLI C 02-3	Version
Order No.	0559900000	CableLine, Mounting mandrel
GTIN (EAN)	4008190081645	
Qty.	20 pc(s).	

CLI C 02-3 RT/WS + CD

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

A - Z



The CableLine range of wire and cable marker products provides users with solutions for the most diverse applications. The range of applications extends from narrow wires right up to cables with large outside diameters.

General ordering data

Type	CLI R 02-3 GE/SW W	Version
Order No.	0560001684	CableLine, Mounting mandrel
GTIN (EAN)	4008190990046	
Qty.	10 pc(s).	
Type	CLI R 02-3 GE/SW H	Version
Order No.	0560001652	CableLine, Mounting mandrel
GTIN (EAN)	4008190989897	
Qty.	10 pc(s).	
Type	CLI R 02-3 GE/SW C	Version
Order No.	0560001642	CableLine, Mounting mandrel
GTIN (EAN)	4008190989842	
Qty.	10 pc(s).	
Type	CLI R 02-3 GE/SW R	Version
Order No.	0560001672	CableLine, Mounting mandrel
GTIN (EAN)	4008190989996	
Qty.	10 pc(s).	
Type	CLI R 02-3 GE/SW D	Version
Order No.	0560001644	CableLine, Mounting mandrel
GTIN (EAN)	4008190989859	
Qty.	10 pc(s).	
Type	CLI R 02-3 GE/SW T	Version
Order No.	0560001678	CableLine, Mounting mandrel
GTIN (EAN)	4008190990015	
Qty.	10 pc(s).	
Type	CLI R 02-3 GE/SW V	Version
Order No.	0560001682	CableLine, Mounting mandrel
GTIN (EAN)	4008190990039	
Qty.	10 pc(s).	
Type	CLI R 02-3 GE/SW U	Version
Order No.	0560001680	CableLine, Mounting mandrel
GTIN (EAN)	4008190990022	
Qty.	10 pc(s).	
Type	CLI R 02-3 GE/SW Q	Version
Order No.	0560001670	CableLine, Mounting mandrel
GTIN (EAN)	4008190989899	
Qty.	10 pc(s).	
Type	CLI R 02-3 GE/SW G	Version
Order No.	0560001650	CableLine, Mounting mandrel
GTIN (EAN)	4008190989880	
Qty.	10 pc(s).	

Creation date January 26, 2022 7:52:36 AM CET

CLI C 02-3 RT/WS + CD

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Type	CLI R 02-3 GE/SW X	Version
Order No.	0560001693	CableLine, Mounting mandrel
GTIN (EAN)	4008190990053	
Qty.	10 pc(s).	
Type	CLI R 02-3 GE/SW B	Version
Order No.	0560001640	CableLine, Mounting mandrel
GTIN (EAN)	4008190989835	
Qty.	10 pc(s).	
Type	CLI R 02-3 GE/SW O	Version
Order No.	0560001666	CableLine, Mounting mandrel
GTIN (EAN)	4008190989965	
Qty.	10 pc(s).	
Type	CLI R 02-3 GE/SW Y	Version
Order No.	0560001697	CableLine, Mounting mandrel
GTIN (EAN)	4008190990060	
Qty.	10 pc(s).	
Type	CLI R 02-3 GE/SW F	Version
Order No.	0560001648	CableLine, Mounting mandrel
GTIN (EAN)	4008190989873	
Qty.	10 pc(s).	
Type	CLI R 02-3 GE/SW N	Version
Order No.	0560001664	CableLine, Mounting mandrel
GTIN (EAN)	4008190989958	
Qty.	10 pc(s).	
Type	CLI R 02-3 GE/SW I	Version
Order No.	0560001654	CableLine, Mounting mandrel
GTIN (EAN)	4008190989903	
Qty.	10 pc(s).	
Type	CLI R 02-3 GE/SW P	Version
Order No.	0560001668	CableLine, Mounting mandrel
GTIN (EAN)	4008190989972	
Qty.	10 pc(s).	
Type	CLI R 02-3 GE/SW J	Version
Order No.	0560001656	CableLine, Mounting mandrel
GTIN (EAN)	4008190989910	
Qty.	10 pc(s).	
Type	CLI R 02-3 GE/SW A	Version
Order No.	0560001638	CableLine, Mounting mandrel
GTIN (EAN)	4008190989828	
Qty.	10 pc(s).	
Type	CLI R 02-3 GE/SW L	Version
Order No.	0560001660	CableLine, Mounting mandrel
GTIN (EAN)	4008190989934	
Qty.	10 pc(s).	
Type	CLI R 02-3 GE/SW K	Version
Order No.	0560001658	CableLine, Mounting mandrel
GTIN (EAN)	4008190989927	
Qty.	10 pc(s).	
Type	CLI R 02-3 GE/SW M	Version
Order No.	0560001662	CableLine, Mounting mandrel
GTIN (EAN)	4008190989941	
Qty.	10 pc(s).	

Creation date January 26, 2022 7:52:36 AM CET

Catalogue status 14.01.2022 / We reserve the right to make technical changes.

CLI C 02-3 RT/WS + CD

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Type	CLI R 02-3 GE/SW E	Version
Order No.	0560001646	CableLine, Mounting mandrel
GTIN (EAN)	4008190989866	
Qty.	10 pc(s).	
Type	CLI R 02-3 GE/SW Z	Version
Order No.	0560001699	CableLine, Mounting mandrel
GTIN (EAN)	4008190990077	
Qty.	10 pc(s).	
Type	CLI R 02-3 GE/SW S	Version
Order No.	0560001675	CableLine, Mounting mandrel
GTIN (EAN)	4008190990008	
Qty.	10 pc(s).	

Special characters



The CableLine range of wire and cable marker products provides users with solutions for the most diverse applications. The range of applications extends from narrow wires right up to cables with large outside diameters.

General ordering data

Type	CLI R 02-3 GE/SW ET	Version
Order No.	0560001745	CableLine, Mounting mandrel
GTIN (EAN)	4008190990121	
Qty.	10 pc(s).	
Type	CLI R 02-3 GE/SW .	Version
Order No.	0560001749	CableLine, Mounting mandrel
GTIN (EAN)	4008190990138	
Qty.	10 pc(s).	
Type	CLI R 02-3 GE/SW -	Version
Order No.	0560001740	CableLine, Mounting mandrel
GTIN (EAN)	4008190990091	
Qty.	10 pc(s).	
Type	CLI R 02-3 GE/SW /	Version
Order No.	0560001743	CableLine, Mounting mandrel
GTIN (EAN)	4008190990114	
Qty.	10 pc(s).	
Type	CLI R 02-3 GE/SW +	Version
Order No.	0560001738	CableLine, Mounting mandrel
GTIN (EAN)	4008190990084	
Qty.	10 pc(s).	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1568241737](#)