

## WQB B/4

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Product image



## General ordering data

|            |                                                                     |
|------------|---------------------------------------------------------------------|
| Version    | W-Series, Cross-connector, For the terminals,<br>Number of poles: 4 |
| Order No.  | <a href="#">1579030000</a>                                          |
| Type       | WQB B/4                                                             |
| GTIN (EAN) | 4008190185046                                                       |
| Qty.       | 50 pc(s).                                                           |

## WQB B/4

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |          |                 |            |
|------------|----------|-----------------|------------|
| Depth      | 2.5 mm   | Depth (inches)  | 0.098 inch |
| Height     | 23.5 mm  | Height (inches) | 0.925 inch |
| Width      | 20.42 mm | Width (inches)  | 0.804 inch |
| Net weight | 1.3 g    |                 |            |

## Temperatures

|                     |                |                                  |       |
|---------------------|----------------|----------------------------------|-------|
| Storage temperature | -25 °C...55 °C | Continuous operating temp., max. | 70 °C |
|---------------------|----------------|----------------------------------|-------|

## Material data

|          |               |        |       |
|----------|---------------|--------|-------|
| Material | tinned copper | Colour | black |
|----------|---------------|--------|-------|

## System specifications

|         |                   |
|---------|-------------------|
| Version | For the terminals |
|---------|-------------------|

## Additional technical data

|                          |                 |                     |                 |
|--------------------------|-----------------|---------------------|-----------------|
| Explosion-tested version | No              | Installation advice | Direct mounting |
| Type of fixing           | when screwed in |                     |                 |

## Cross-connector

|                                     |                 |                           |      |
|-------------------------------------|-----------------|---------------------------|------|
| Number of cross-connected terminals | 4               | Rated current, multi-pole | 24 A |
| Type                                | Cross-connector |                           |      |

## Dimensions

|                 |        |
|-----------------|--------|
| Pitch in mm (P) | 5.1 mm |
|-----------------|--------|

## General

|                     |                 |                 |   |
|---------------------|-----------------|-----------------|---|
| Installation advice | Direct mounting | Number of poles | 4 |
|---------------------|-----------------|-----------------|---|

## Rating data

|               |     |
|---------------|-----|
| Rated voltage | 800 |
|---------------|-----|

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000489    | ETIM 7.0    | EC000489    |
| ETIM 8.0    | EC000489    | ECLASS 9.0  | 27-14-11-40 |
| ECLASS 9.1  | 27-14-11-40 | ECLASS 10.0 | 27-14-11-40 |
| ECLASS 11.0 | 27-14-11-40 |             |             |

## Approvals

|           |  |
|-----------|--|
| Approvals |  |
|-----------|--|



|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## WQB B/4

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

|                                             |                                                 |
|---------------------------------------------|-------------------------------------------------|
| Approval/Certificate/Document of Conformity | <a href="#">EAC certificate</a>                 |
| Engineering Data                            | <a href="#">CAD data – STEP</a>                 |
| Engineering Data                            | <a href="#">EPLAN, WSCAD, Zuken E3.S</a>        |
| User Documentation                          | <a href="#">StorageConditionsTerminalBlocks</a> |
| Catalogues                                  | <a href="#">Catalogues in PDF-format</a>        |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1579030000](#)