

KV 11-M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

General ordering data

Version	VG H (HDC halved cable gland), Cable glands, PG 11, IP65, Brass, nickel-plated
Order No.	1656390000
Type	KV 11-M
GTIN (EAN)	4008190409401
Qty.	10 pc(s).

KV 11-M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight	9 g
------------	-----

Temperatures

Operating temperature	-20 °C...60 °C
-----------------------	----------------

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

General information

AF size 1	10 mm	Cable glands	PG
External thread	PG 11	Material	Brass, nickel-plated
Notch multi-layer sealing diameter 1	7.5 mm	Notch multi-layer sealing diameter 2	10 mm
Notch multi-layer sealing diameter 3	12.5 mm	O-Ring	NBR
Operating temperature range, max.	60 °C	Operating temperature range, min.	-20 °C
Protection degree	IP65	Protection degree with GWDR	IP65

Classifications

ETIM 6.0	EC000441	ETIM 7.0	EC000441
ETIM 8.0	EC000441	ECLASS 9.0	27-14-44-32
ECLASS 9.1	27-14-44-32	ECLASS 10.0	27-14-44-32
ECLASS 11.0	27-14-44-32		

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN, WSCAD
Catalogues	Catalogues in PDF-format
Brochures	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1656390000](#)