

SCT 4.6/360 C**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

Weidmüller stainless steel Series contains a comprehensive assortment of stainless steel cable ties for extreme conditions such as high temperatures or severe chemical effects.

- stainless steel AISI 316,
- ideal for use outdoors,
- radiation- and corrosion-resistant,
- anti-magnetic,
- no serrations, so no damage to the insulation.

General ordering data

Version	Cable ties, 4.6 x 360 mm, Stainless steel 1.4301, 445 N
Order No.	1699910000
Type	SCT 4.6/360 C
GTIN (EAN)	4008190892357
Qty.	100 pc(s).
Delivery status	This article will no longer be available in the future.
Available until	2022-06-30
Alternative product	2791410000

Creation date September 16, 2022 9:18:46 AM CEST

SCT 4.6/360 C

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	0.25 mm	Depth (inches)	0.01 inch
Height	360 mm	Height (inches)	14.173 inch
Width	4.6 mm	Width (inches)	0.181 inch
Net weight	3.5 g		

Temperatures

Operating temperature range	-80...538 °C
-----------------------------	--------------

Installation materials

Cable diameter, max.	101 mm	For re-opening	No
Halogen	No	Material	Stainless steel 1.4301
Operating temperature range, max.	538 °C	Operating temperature range, min.	-80 °C
Tensile strength	445 N	Tensile strength (Pound-force)	100 lbf
UV-resistant	No		

Classifications

ETIM 6.0	EC000046	ETIM 7.0	EC000046
ETIM 8.0	EC000046	ECLASS 9.0	27-14-07-02
ECLASS 9.1	27-14-07-02	ECLASS 10.0	27-14-07-02
ECLASS 11.0	27-14-07-02	ECLASS 12.0	27-14-07-02

Approvals

Approvals



ROHS

Conform

Downloads

Engineering Data	EPLAN, WSCAD
Catalogues	Catalogues in PDF-format


SCT 4.6/360 C

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Drawing



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1699910000](#)