

MARKO-C.100X100X100 B/DR**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**General ordering data**

Version	Device markers, Device markers, 100 x 100 mm, yellow
Order No.	1700550001
Type	MARKO-C.100X100X100 B/DR
GTIN (EAN)	4008 1908962 18
Qty.	10 pc(s).

MARKO-C.100X100X100 B/DR**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	0.05 mm	Depth (inches)	0.002 inch
Height	100 mm	Height (inches)	3.937 inch
Width	100 mm	Width (inches)	3.937 inch
Net weight	5.8 g		

Temperatures

Operating temperature range	-29...80 °C
-----------------------------	-------------

General data

Adhesive	Permanent acrylic copolymer	Colour	yellow
Colour of printing	black	Material	Acrylic-coated fibre webbing
Material colour according to resistance code	4	Number of markers per combination	1 Label sheet = 3 Device markers
Operating temperature range	-29...80 °C	Operating temperature range, max.	80 °C
Operating temperature range, min.	-29 °C	Printed characters	Symbols
Printing	Lightning flash in triangle	Version	Self-adhesive
Width	100 mm		

Classifications

ETIM 6.0	EC001288	ETIM 7.0	EC001288
ETIM 8.0	EC001288	ECLASS 9.0	27-40-06-29
ECLASS 9.1	27-40-06-29	ECLASS 10.0	27-40-06-29
ECLASS 11.0	27-28-11-04	ECLASS 12.0	27-28-11-04

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN, WSCAD
Catalogues	Catalogues in PDF-format

MARKO-C.100X100X100 B/DR

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1700550001](#)