

KLBUE 15-32**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image****Shielding and earthing**

Our protective earth conductor and shielding terminals featuring different connection technologies allow you to effectively protect both people and equipment from interference, such as electrical or magnetic fields. A comprehensive range of accessories rounds off our range.

General ordering data

Version	Clamping yoke, Clamping yoke, Steel
Order No.	1716300000
Type	KLBUE 15-32
GTIN (EAN)	4008190350499
Qty.	10 pc(s).

KLBUE 15-32**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	64 mm	Depth (inches)	2.52 inch
Height	32 mm	Height (inches)	1.26 inch
Width	33.5 mm	Width (inches)	1.319 inch
Net weight	79.1 g		

Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

Material data

Material	Steel	Colour	silver
----------	-------	--------	--------

System specifications

Version	For a shield connection
---------	-------------------------

Additional technical data

Explosion-tested version	Yes	Installation advice	Busbar
Type of fixing	Snap-on		

Conductors for clamping (rated connection)

Cable diameter, max.	32 mm	Cable diameter, min.	15 mm
----------------------	-------	----------------------	-------

Dimensions

Pitch in mm (P)	36 mm
-----------------	-------

General

Installation advice	Busbar
---------------------	--------

Classifications

ETIM 6.0	EC002020	ETIM 7.0	EC002020
ETIM 8.0	EC002020	ECLASS 9.0	27-14-11-50
ECLASS 9.1	27-14-11-50	ECLASS 10.0	27-14-11-50
ECLASS 11.0	27-14-11-50		

Approvals

Approvals



ROHS	Conform
------	---------

KLBUE 15-32

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

Approval/Certificate/Document of Conformity	Attestation of Conformity EAC certificate
Engineering Data	CAD data – STEP
Engineering Data	EPLAN, WSCAD
User Documentation	Beipackzettel_KLBUE.pdf StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format
Brochures	

KLBUE 15-32

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Mounting support




Shielding and earthing

Our protective earth conductor and shielding terminals featuring different connection technologies allow you to effectively protect both people and equipment from interference, such as electrical or magnetic fields. A comprehensive range of accessories rounds off our range.

General ordering data

Type	WSH 3/H/N	Version
Order No.	1715970000	Accessories, Rail support, Wemid
GTIN (EAN)	4008190353100	
Qty.	10 pc(s).	
Type	WSH 1	Version
Order No.	1068700000	Accessories, Rail support, PA 66 GF 30
GTIN (EAN)	4008190118389	
Qty.	10 pc(s).	
Type	WSH 6	Version
Order No.	1080200000	Accessories, Rail support, Wemid
GTIN (EAN)	4008190965150	
Qty.	10 pc(s).	
Type	WSH 5	Version
Order No.	1080100000	Accessories, Rail support, Wemid
GTIN (EAN)	4008190965143	
Qty.	10 pc(s).	

Copper



Of all the metals used, copper has the best electrical conductivity, which results in the highest short-circuit resistance. This makes the copper busbar the most widely used variant.

General ordering data

Type	SSCH 10X3X1000 CU/SN	Version
Order No.	0348900000	Accessories, Busbar, Copper
GTIN (EAN)	4008190024802	
Qty.	1 m	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1716300000](#)