

FM 4.2/TS35**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image****Shielding and earthing**

Our protective earth conductor and shielding terminals featuring different connection technologies allow you to effectively protect both people and equipment from interference, such as electrical or magnetic fields. A comprehensive range of accessories rounds off our range.

General ordering data

Version	Accessories, Mounting foot, Steel, bright finish
Order No.	1724580000
Type	FM 4.2/TS35
GTIN (EAN)	4008190377717
Qty.	40 pc(s).

FM 4.2/TS35

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	7 mm	Depth (inches)	0.276 inch
Height	50.2 mm	Height (inches)	1.976 inch
Width	14 mm	Width (inches)	0.551 inch
Net weight	4.5 g		

Material data

Material	Steel, bright finish	Surface finish	nickel-plated
Colour	silver		

System specifications

Version	For the mounting rails	Rail	TS 35
---------	------------------------	------	-------

Additional technical data

Explosion-tested version	No	Type of fixing	Snap-on
--------------------------	----	----------------	---------

Dimensions

Pitch in mm (P)	14 mm
-----------------	-------

General

Rail	TS 35	Surface finish	nickel-plated
------	-------	----------------	---------------

Classifications

ETIM 6.0	EC002625	ETIM 7.0	EC002625
ETIM 8.0	EC002625	ECLASS 9.0	27-18-28-07
ECLASS 9.1	23-15-90-90	ECLASS 10.0	27-18-28-07
ECLASS 11.0	27-18-28-07		

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Engineering Data	WSCAD, EPLAN
User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format
Brochures	

FM 4.2/TS35

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1724580000](#)