

**ESG 7/20 SIRIUS MC NE WS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from manufacturers like Siemens, ABB, Beckhoff etc.

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

|                    |                                                                                  |
|--------------------|----------------------------------------------------------------------------------|
| Version            | ESG, Device markers x 20 mm, PA 66, Colour: white, pluggable                     |
| Order No.          | <a href="#">1736181044</a>                                                       |
| Type               | ESG 7/20 SIRIUS MC NE WS                                                         |
| GTIN (EAN)         | 4008190985950                                                                    |
| Qty.               | 200 pc(s).                                                                       |
| compatible printer | <a href="#">2715590000</a> <a href="#">2438520000</a> <a href="#">2438510000</a> |

## ESG 7/20 SIRIUS MC NE WS

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 0.8 mm  | Depth (inches)  | 0.031 inch |
| Height     | 7 mm    | Height (inches) | 0.276 inch |
| Width      | 20 mm   | Width (inches)  | 0.787 inch |
| Net weight | 0.515 g |                 |            |

## Temperatures

|                             |              |
|-----------------------------|--------------|
| Operating temperature range | -40...100 °C |
|-----------------------------|--------------|

## General data

|                                              |                   |                                   |                              |
|----------------------------------------------|-------------------|-----------------------------------|------------------------------|
| Application/manufacture                      | Siemens Sirius 3R | Colour                            | white                        |
| Halogen                                      | No                | Material                          | PA 66                        |
| Material colour according to resistance code | 9                 | Number of markers per combination | 1 MultiCard = Device markers |
| Number per roll                              | 40                | Number per sheet                  | 40                           |
| Operating temperature range                  | -40...100 °C      | Operating temperature range, max. | 100 °C                       |
| Operating temperature range, min.            | -40 °C            | UL 94 flammability rating         | V-2                          |
| Version                                      | pluggable         | Width                             | 20 mm                        |

## Device markers

|         |    |
|---------|----|
| Halogen | No |
|---------|----|

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001288    | ETIM 7.0    | EC001288    |
| ETIM 8.0    | EC001288    | ECLASS 9.0  | 27-40-06-29 |
| ECLASS 9.1  | 27-40-06-29 | ECLASS 10.0 | 27-40-06-29 |
| ECLASS 11.0 | 27-28-11-04 | ECLASS 12.0 | 27-28-11-04 |

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Downloads

|                             |                                                                                                                            |
|-----------------------------|----------------------------------------------------------------------------------------------------------------------------|
| Engineering Data            | <a href="#">CAD data – STEP</a>                                                                                            |
| Engineering Data            | <a href="#">EPLAN, WSCAD</a>                                                                                               |
| Product Change Notification | <a href="#">Technical change to MultiCard material - DE</a><br><a href="#">Technical change to MultiCard material - EN</a> |
| Catalogues                  | <a href="#">Catalogues in PDF-format</a>                                                                                   |
| Brochures                   |                                                                                                                            |

**ESG 7/20 SIRIUS MC NE WS**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1736181044](#)