

KLBUE 4-13.5 CPF**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image****Shielding and earthing**

Our protective earth conductor and shielding terminals featuring different connection technologies allow you to effectively protect both people and equipment from interference, such as electrical or magnetic fields. A comprehensive range of accessories rounds off our range.

General ordering data

Version	Clamping yoke, Clamping yoke, Steel
Order No.	1752691001
Type	KLBUE 4-13.5 CPF
GTIN (EAN)	4032248044429
Qty.	10 pc(s).

KLBUE 4-13.5 CPF

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	31.5 mm	Depth (inches)	1.24 inch
Height	22 mm	Height (inches)	0.866 inch
Width	20.5 mm	Width (inches)	0.807 inch
Mounting dimension - width	19 mm	Net weight	23.1 g

Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

Material data

Material	Steel	Colour	grey
----------	-------	--------	------

System specifications

Version	For a shield connection	Rail	TS 27
---------	-------------------------	------	-------

Additional technical data

Explosion-tested version	Yes	Installation advice	Direct mounting
Type of fixing	when screwed in		

Conductors for clamping (rated connection)

Cable diameter, max.	13.5 mm	Cable diameter, min.	4 mm
----------------------	---------	----------------------	------

Dimensions

Pitch in mm (P)	20 mm
-----------------	-------

General

Installation advice	Direct mounting	Rail	TS 27
---------------------	-----------------	------	-------

Classifications

ETIM 6.0	EC002020	ETIM 7.0	EC002020
ETIM 8.0	EC002020	ECLASS 9.0	27-14-11-50
ECLASS 9.1	27-14-11-50	ECLASS 10.0	27-14-11-50
ECLASS 11.0	27-14-11-50		

Approvals

Approvals



ROHS	Conform
------	---------

KLBUE 4-13.5 CPF

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

Approval/Certificate/Document of
Conformity

[EAC certificate](#)

Engineering Data

[CAD data – STEP](#)

Engineering Data

[EPLAN, WSCAD](#)

User Documentation

[Beipackzettel_KLBUE.pdf](#)
[StorageConditionsTerminalBlocks](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures

KLBUE 4-13.5 CPF**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Steel**

Steel DIN rails are the most widespread on the market. Among metal DIN rails, they have the lowest shortcircuit protection, similar to stainless steel.

General ordering data

Type	TS 27X12.5M/ST/F.ZN	Version
Order No.	1802690000	Terminal rails, Rail, DIN EN 60715, Steel
GTIN (EAN)	4032248257201	
Qty.	2 m	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1752691001](#)