

**KLBUE 4-13.5 CPF****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

Thanks to special mounting feet, the product portfolio also includes shield clamping saddles that can be mounted on the C-profiles. The shield is diverted from the shield clamping saddles via the mounting foot to the C-profiles and thus to PE (ground).

**General ordering data**

|            |                                     |
|------------|-------------------------------------|
| Version    | Clamping yoke, Clamping yoke, Steel |
| Order No.  | <a href="#">1752691001</a>          |
| Type       | KLBUE 4-13.5 CPF                    |
| GTIN (EAN) | 4032248044429                       |
| Qty.       | 10 pc(s).                           |

## KLBUE 4-13.5 CPF

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|                            |         |                 |            |
|----------------------------|---------|-----------------|------------|
| Depth                      | 31.5 mm | Depth (inches)  | 1.24 inch  |
| Height                     | 22 mm   | Height (inches) | 0.866 inch |
| Width                      | 20.5 mm | Width (inches)  | 0.807 inch |
| Mounting dimension - width | 19 mm   | Net weight      | 23.1 g     |

## Temperatures

|                     |                |
|---------------------|----------------|
| Storage temperature | -25 °C...55 °C |
|---------------------|----------------|

## Material data

|          |       |        |      |
|----------|-------|--------|------|
| Material | Steel | Colour | grey |
|----------|-------|--------|------|

## System specifications

|         |                         |      |       |
|---------|-------------------------|------|-------|
| Version | For a shield connection | Rail | TS 27 |
|---------|-------------------------|------|-------|

## Additional technical data

|                          |                 |                     |                 |
|--------------------------|-----------------|---------------------|-----------------|
| Explosion-tested version | Yes             | Installation advice | Direct mounting |
| Type of fixing           | when screwed in |                     |                 |

## Conductors for clamping (rated connection)

|                      |         |                      |      |
|----------------------|---------|----------------------|------|
| Cable diameter, max. | 13.5 mm | Cable diameter, min. | 4 mm |
|----------------------|---------|----------------------|------|

## Dimensions

|                 |       |
|-----------------|-------|
| Pitch in mm (P) | 20 mm |
|-----------------|-------|

## General

|                     |                 |      |       |
|---------------------|-----------------|------|-------|
| Installation advice | Direct mounting | Rail | TS 27 |
|---------------------|-----------------|------|-------|

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002020    | ETIM 7.0    | EC002020    |
| ETIM 8.0    | EC002020    | ECLASS 9.0  | 27-14-11-50 |
| ECLASS 9.1  | 27-14-11-50 | ECLASS 10.0 | 27-14-11-50 |
| ECLASS 11.0 | 27-14-11-50 | ECLASS 12.0 | 27-14-11-50 |

## Approvals

Approvals



|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### KLBUE 4-13.5 CPF

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

Approval/Certificate/Document of  
Conformity

[EAC certificate](#)

Engineering Data

[CAD data – STEP](#)

Engineering Data

[EPLAN, WSCAD](#)

User Documentation

[Beipackzettel\\_KLBUE.pdf](#)  
[StorageConditionsTerminalBlocks](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1752691001](#)