

HDC CM 3 MC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The module is assembled with HE crimp contacts. The crimp contact features a stainless steel spring. The provides a secure snap-in contact with the module. A customized contact removal tool is available for removing the contacts.

The power modules can be ordered with or without the integrated module release aid. A removal tool is available for modules that do not have the integrated module release aid.

General ordering data

Version	Heavy-duty connectors, HDC insert, ConCept module
Order No.	1758360000
Type	HDC CM 3 MC
GTIN (EAN)	4032248019588
Qty.	10 pc(s).

HDC CM 3 MC

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	34 mm	Depth (inches)	1.339 inch
Height	31.4 mm	Height (inches)	1.236 inch
Width	11.4 mm	Width (inches)	0.449 inch
Net weight	6.8 g		

ConCept Pneumatic module

Colour	beige	UL 94 flammability rating	V-0
--------	-------	---------------------------	-----

Dimensions

Height of plug	31.4 mm	Total length base	34 mm
Width	11.4 mm		

General data

Insulation strength	$10^{12} \Omega$	Material	Polycarbonate, glass fibre reinforced
Number of poles	3	Pollution severity	3
Rated current (DIN EN 61984)	40 A	Rated impulse voltage (DIN EN 61984)	8 kV
Rated voltage (DIN EN 61984)	690 V	Series	ConCept module
Surge voltage category	III	Type	Pin
UL 94 flammability rating	V-0	Volume resistance	$\leq 1 \text{ m}\Omega$

Connection data PE

Connection type PE	Screw connection via module frame
--------------------	-----------------------------------

Version

Conductor cross-section, max.	10 mm ²	Conductor cross-section, min.	1.5 mm ²
Material	Polycarbonate, glass fibre reinforced	Stripping length, rated connection	10 mm
Type of connection	Crimp connection	Volume resistance	$\leq 1 \text{ m}\Omega$
Wire connection cross section AWG, max.	AWG 7	Wire connection cross section AWG, min.	AWG 16

Classifications

ETIM 6.0	EC000438	ETIM 7.0	EC000438
ETIM 8.0	EC000438	ECLASS 9.0	27-44-02-05
ECLASS 9.1	27-44-02-05	ECLASS 10.0	27-44-02-05
ECLASS 11.0	27-44-02-05	ECLASS 12.0	27-44-02-05

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E92202

HDC CM 3 MC

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads


Approval/Certificate/Document of Conformity	Manufacturer's declaration
Engineering Data	CAD data – STEP
Engineering Data	WSCAD
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN

HDC CM 3 MC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1758360000](#)