

**CLI T 3-15****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration

The CLI T sleeve is a high-quality, transparent sleeve for marking conductors and cables with cross-sections up to 75 mm<sup>2</sup>. The CLI T sleeve is available in four lengths so that labelling with long character strings is possible. The transparent sleeve optimally protects the inlay tag against outside influences. As inlay tag the TM-I marker from the MultiCard and MultiMark portfolio be suitable.

- Wider cross-section range per sleeve
- A special flexible bellow profile ensures a wide application range
- Easy insertion of the TM-I tag into the sleeve pocket before or after connecting the conductor
- Available in five lengths
- Not suitable for labelling with P-Ink or STI pen

**General ordering data**

|            |                                                                               |
|------------|-------------------------------------------------------------------------------|
| Version    | CableLine, Socket x 5 mm, PVC, Colour: Transparent, Conductor O.D.: 8 - 16 mm |
| Order No.  | <a href="#">1764280000</a>                                                    |
| Type       | CLI T 3-15                                                                    |
| GTIN (EAN) | 4032248053346                                                                 |
| Qty.       | 100 pc(s).                                                                    |

## CLI T 3-15

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |        |                 |            |
|------------|--------|-----------------|------------|
| Depth      | 19 mm  | Depth (inches)  | 0.748 inch |
| Height     | 15 mm  | Height (inches) | 0.591 inch |
| Width      | 5 mm   | Width (inches)  | 0.197 inch |
| Net weight | 1.02 g |                 |            |

## Temperatures

|                             |             |
|-----------------------------|-------------|
| Operating temperature range | -30...80 °C |
|-----------------------------|-------------|

## General data

|                                   |                           |                                   |             |
|-----------------------------------|---------------------------|-----------------------------------|-------------|
| Colour                            | Transparent               | Halogen                           | Yes         |
| Material                          | PVC                       | Operating temperature range       | -30...80 °C |
| Operating temperature range, max. | 80 °C                     | Operating temperature range, min. | -30 °C      |
| Recommended industries            | Transportation, Machinery | Type of printing                  | neutral     |
| UL 94 flammability rating         | V-0                       | Width                             | 5 mm        |

## Conductor and cable markers

|                               |                    |                                  |                         |
|-------------------------------|--------------------|----------------------------------|-------------------------|
| Conductor O.D.                | 8 - 16 mm          | Conductor O.D., max.             | 16 mm                   |
| Conductor O.D., min.          | 8 mm               | Conductor cross-section, max.    | 75 mm <sup>2</sup>      |
| Conductor cross-section, min. | 25 mm <sup>2</sup> | Cross-section for connected wire | 25 - 75 mm <sup>2</sup> |
| Halogen                       | Yes                |                                  |                         |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001530    | ETIM 7.0    | EC001530    |
| ETIM 8.0    | EC001530    | ECLASS 9.0  | 27-40-04-01 |
| ECLASS 9.1  | 27-40-04-01 | ECLASS 10.0 | 27-40-04-01 |
| ECLASS 11.0 | 27-28-11-02 |             |             |

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Downloads

|                             |                                                                                          |
|-----------------------------|------------------------------------------------------------------------------------------|
| Engineering Data            | <a href="#">EPLAN, WSCAD</a>                                                             |
| Product Change Notification | <a href="#">PCN Transparent Sleeves_DE</a><br><a href="#">PCN Transparent Sleeves_EN</a> |
| Catalogues                  | <a href="#">Catalogues in PDF-format</a>                                                 |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1764280000](#)