

GWDR M63-PO**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	GWDR PO (flat gasket - polyethylene), Sealing ring, M 63, Polyethylene
Order No.	1777990000
Type	GWDR M63-PO
GTIN (EAN)	4032248158256
Qty.	50 pc(s).

GWDR M63-PO**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight	1.42 g
------------	--------

Temperatures

Operating temperature	-30 °C...90 °C
-----------------------	----------------

General information

Cable glands	M 63	Diameter of sealing ring	70 mm
External thread	M 63	Inside diameter D2	63 mm
Material	Polyethylene	O.D.	70 mm
Operating temperature range, max.	90 °C	Operating temperature range, min.	-30 °C
Pitch of thread	1.5 mm	Sealing	PE-HD
Silicone	Yes	Thickness	2 mm

Classifications

ETIM 6.0	EC001181	ETIM 7.0	EC001181
ETIM 8.0	EC001181	ECLASS 9.0	27-43-03-19
ECLASS 9.1	27-14-44-90	ECLASS 10.0	27-43-03-19
ECLASS 11.0	27-43-03-19	ECLASS 12.0	27-43-03-19

Approvals

ROHS	Conform
------	---------

Downloads


Engineering Data	CAD data – STEP
Engineering Data	EPLAN, WSCAD
Catalogues	Catalogues in PDF-format
Brochures	

GWDR M63-PO

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1777990000](#)