

**HDC 24B KBU 1M25G****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

**General ordering data**

|            |                                                                                                                                                                    |
|------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Version    | HDC enclosures, Size: 8, Protection degree: IP65 (in plugged condition), Coupling housing, Side-locking clamp on lower side, Standard, Size of cable entries: M 25 |
| Order No.  | <a href="#">1787920000</a>                                                                                                                                         |
| Type       | HDC 24B KBU 1M25G                                                                                                                                                  |
| GTIN (EAN) | 4032248205363                                                                                                                                                      |
| Qty.       | 1 pc(s).                                                                                                                                                           |

## HDC 24B KBU 1M25G

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |       |                 |            |
|------------|-------|-----------------|------------|
| Height     | 65 mm | Height (inches) | 2.559 inch |
| Width      | 55 mm | Width (inches)  | 2.165 inch |
| Net weight | 342 g |                 |            |

## Temperatures

|                   |                   |
|-------------------|-------------------|
| Limit temperature | -40 °C ... 125 °C |
|-------------------|-------------------|

## Environmental Product Compliance

|                     |                                                                |                         |
|---------------------|----------------------------------------------------------------|-------------------------|
| REACH SVHC          | Lead 7439-92-1, Potassium perfluorobutane sulfonate 29420-49-3 |                         |
| SCIP                | e98b2b24-ba23-41bf-8d19-0dda3647412f                           |                         |
| Chemical resistance | Substance                                                      | Acetone                 |
|                     | Chemical resistance                                            | Conditionally resistant |
|                     | Substance                                                      | Drilling oil            |
|                     | Chemical resistance                                            | Resistant               |
|                     | Substance                                                      | Diesel                  |
|                     | Chemical resistance                                            | Resistant               |
|                     | Substance                                                      | Ethyl alcohol           |
|                     | Chemical resistance                                            | Resistant               |
|                     | Substance                                                      | Transmission oil        |
|                     | Chemical resistance                                            | Resistant               |
|                     | Substance                                                      | Hydraulic oil           |
|                     | Chemical resistance                                            | Resistant               |
|                     | Substance                                                      | Coolant                 |
|                     | Chemical resistance                                            | Resistant               |
|                     | Substance                                                      | Petroleum benzine       |
|                     | Chemical resistance                                            | Resistant               |
|                     | Substance                                                      | Sweat                   |
|                     | Chemical resistance                                            | Resistant               |
|                     | Substance                                                      | Premium gasoline        |
|                     | Chemical resistance                                            | Conditionally resistant |
|                     | Substance                                                      | Water                   |
|                     | Chemical resistance                                            | Resistant               |
|                     | Substance                                                      | UV                      |
|                     | Chemical resistance                                            | Unstable                |
|                     | Substance                                                      | Ozone                   |
|                     | Chemical resistance                                            | Unstable                |

## Dimensions

|                      |           |                     |       |
|----------------------|-----------|---------------------|-------|
| Cable entry          | w. thread | Height of housing B | 65 mm |
| Total length housing | 120 mm    | Width housing C     | 43 mm |

## General data

|                             |                             |                       |                             |
|-----------------------------|-----------------------------|-----------------------|-----------------------------|
| EMC housings                | No                          | Housing main material | diecast aluminium           |
| Material of locking element | Stainless steel, rust-proof | Protection degree     | IP65 (in plugged condition) |
| Surface finish              | Powder coating              |                       |                             |

## HDC 24B KBU 1M25G

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Version

|                              |                                  |                                |                    |
|------------------------------|----------------------------------|--------------------------------|--------------------|
| BG                           | 8                                | Cable entry                    | w. thread          |
| Clamp version                | Side-locking clamp               | Colour (RAL)                   | RAL 7035           |
| Design                       | Standard                         | Design of housing              | Coupling housing   |
| Design of locking system     | Side-locking clamp on lower side | Internal thread                | M 25               |
| Number of cable entry on top | 1                                | Number of cable entry sideways | 0                  |
| Sealing                      | NBR                              | Size                           | 8                  |
| Size of cable entries        | M 25                             | Suitable for ModuPlug®         | No                 |
| Top part/bottom part/lid     | lower part                       | Type                           | coupling extension |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000437    | ETIM 7.0    | EC000437    |
| ETIM 8.0    | EC000437    | ECLASS 9.0  | 27-44-02-02 |
| ECLASS 9.1  | 27-44-02-02 | ECLASS 10.0 | 27-44-02-02 |
| ECLASS 11.0 | 27-44-02-02 | ECLASS 12.0 | 27-44-02-02 |

## Approvals

Approvals



|                         |            |
|-------------------------|------------|
| ROHS                    | Conform    |
| UL File Number Search   | UL Website |
| Certificate No. (cURus) | E92202     |

## Downloads


|                                             |                                                                                                                            |
|---------------------------------------------|----------------------------------------------------------------------------------------------------------------------------|
| Approval/Certificate/Document of Conformity | <a href="#">Manufacturer's declaration</a>                                                                                 |
| Engineering Data                            | <a href="#">CAD data – STEP</a>                                                                                            |
| Engineering Data                            | <a href="#">EPLAN, WSCAD</a>                                                                                               |
| Product Change Notification                 | <a href="#">20220214 Technical change to HDC housings</a><br><a href="#">20220214 Technische Änderung bei HDC-Gehäusen</a> |
| Technical Documentation                     | <a href="#">1787920000 HDC_24B_KBU_1M25G_STP_Blatt_1.pdf</a>                                                               |
| Catalogues                                  | <a href="#">Catalogues in PDF-format</a>                                                                                   |
| Brochures                                   | <a href="#">FL FIELDWIRING EN</a><br><a href="#">FL FIELDWIRING EN</a>                                                     |

### HDC 24B KBU 1M25G

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1787920000](#)